



SS Stainless Steel

**Type**

- DK** With triangular spindle
- VK** With square spindle
- SCH** With slot

**Metric table**

Dimensions in: millimeters - inches

Latch arm distance <b>A</b>		
7.5 0.30	13.5 0.53	19.5 0.77

**Specification**

- Cam latch housing  
Stainless steel AISI 303
- Latch arm / assembly hardware  
Stainless steel AISI 304
- Protection class IP 65
- *IP Protection Classes* → page 2130
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

**Accessory**

- Socket keys GN 119.2 → page 1310
- Protective caps GN 120 → [www.jwwinco.com](http://www.jwwinco.com)

**Information**

Latches GN 115.6 have smaller dimensions than standard latches GN 115, making them ideal for applications with limited space or requiring an unobtrusive appearance. Thanks to the stainless steel material, the latches are optimally suited for use in harsh environments.

They are operated with a rotation limited to 90°, which moves the latch bar into the locked position behind the frame. The bevels of the latch arm ease the closing of the door.

Latch arms are available with different bend angles to cover a latch arm distance A of 7.5 / 13.5 and 19.5 mm.

The latches GN 115.6 are supplied with loosely enclosed latch arm.

**see also...**

- *Construction and Assembly Instructions* → page 1261
- *List of Cam Latch / Cam Lock Types* → page 1256
- *Cam Latches / Cam Locks GN 115.1 (Zinc Die-Cast, Small Type)* → page 1270
- *Cam Latches GN 115 (Stainless Steel, Operation with Socket Key)* → page 1267
- *Cam Latches GN 115 (Stainless Steel, with Operating Elements)* → page 1266
- *Cam Locks GN 115 (Stainless Steel)* → page 1268

<b>How to order</b>  <b>GN 115.6-VK-19.5</b>	1 Type
	2 Latch arm distance A