



- 1 Type**
- DK** With triangular spindle
 - VK7** With square spindle
 - VK8** With square spindle
 - SCH** With slot
 - VDE** With double bit
- 3 Hook version**
- H1** Pivoting radius R = 28
- 5 Identification no.**
- 1** Without latch bracket
 - 2** With latch bracket

Metric table

2

Dimensions in: millimeters - inches

Hook distance A	d	h
18	28	4
0.71	1.10	0.16

*Dimensions of the latch bracket, see page 1299

Specification

- Cam latch housing
Zinc die-cast
- Housing collar
 - Chrome plated finish **CR**
 - Powder coated
Black, RAL 9005, textured finish **SW**
- Hook / assembly hardware
Steel, zinc plated, blue passivated finish
- Protection class IP65
- IP Protection Classes → page XYZ
- RoHS compliant

Accessory

- Socket keys GN 119.2 → page 1310
- Protective caps GN 120
→ www.jwwinco.com
- Opening handles GN 120.1
→ www.jwwinco.com

On request

- Cam latches with other hook distance A
- Hook with other pivoting radius R

Information

GN 115.8 cam latches with hook and latch bracket are mainly used for sliding doors and flaps. The latching action is in a radial direction to the axis of rotation, resulting in a wide variety of different uses. The latches GN 115.8 are supplied with loosely enclosed hook.

see also...

- Construction and Assembly Instructions → page 1299
- List of Cam Latch / Cam Lock Types → page 1256
- Cam Latches with Hook GN 115.8 (with Operating Elements) → page 1300

How to order	1 Type
GN 115.8-VDE-18-H1-CR-1 1 2 3 4 5	2 Hook distance A
	3 Hook version
	4 Finish (Housing collar)
	5 Identification no.