



Inch table

Dimensions in: inches - millimeters

¹ d ₁	² d ₂			d ₃	h ₁	h ₂	h ₃ ≈	h ₄ Stroke	l ₂	t min.
0.55 14	10 x 32	10 x 24	1/4 x 20	0.39 10	0.98 25	0.18 4.5	1.38 35	0.14 3.5	1.77 45	0.35 9
0.71 18	1/4 x 20	5/16 x 18	-	0.53 13.5	1.22 31	0.26 6.5	1.77 45	0.16 4	2.44 62	0.43 11
0.87 22	5/16 x 18	3/8 x 16	-	0.63 16	1.42 36	0.31 8	2.05 52	0.16 4	2.91 74	0.55 14
0.98 25	3/8 x 16	1/2 x 13	-	0.75 19	1.69 43	0.43 11	2.48 63	0.16 4	3.50 89	0.67 17
1.18 30	1/2 x 13	5/8 x 11	-	0.91 23	1.99 50.5	0.47 12	2.99 76	0.20 5	4.25 108	0.87 22

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂			d ₃	h ₁	h ₂	h ₃ ≈	h ₄ Stroke	l ₂	t min.
14 0.55	M 5	M 6	10 0.39	25 0.98	4.5 0.18	35 1.38	3.5 0.14	45 1.77	9 0.35	
18 0.71	M 6	M 8	13.5 0.53	31 1.22	6.5 0.26	45 1.77	4 0.16	62 2.44	11 0.43	
22 0.87	M 8	M 10	16 0.63	36 1.42	8 0.31	52 2.05	4 0.16	74 2.91	14 0.55	
25 0.98	M 10	M 12	19 0.75	43 1.69	11 0.43	63 2.48	4 0.16	89 3.50	17 0.67	
30 1.18	M 12	M 16	23 0.91	50.5 1.99	12 0.47	76 2.99	5 0.20	108 4.25	22 0.87	

Specification

- Lever body
Zinc die-cast
- Powder coated
Black, RAL 9005, textured finish **● SW**
Orange, RAL 2004, textured finish **● OS**
- Tapped insert / retaining screw
Steel, blackened finish
- RoHS compliant

On request

- Special colors and threads

Information

GN 101 adjustable levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

How to order (Inch)	¹ Diameter d ₁
² GN 101-14-10X32-SW	² Thread d ₂
³	³ Color

How to order (Metric)	¹ Diameter d ₁
² GN 101-25-M12-OS	² Thread d ₂
³	³ Color