



SS Stainless Steel

1 Type

- SKN** With wing knob
- STN** With T-handle

Metric table

2

Dimensions in: millimeters - inches

Latch arm distance A								
6	10	14	18	20	22	24	26	28
0.24	0.39	0.55	0.71	0.79	0.87	0.94	1.02	1.10

Specification

3

- Cam latch housing / Operating elements
Stainless steel AISI 316 **A4**
- Latch arm
Stainless steel AISI 316
- Other parts
Stainless steel AISI 316
- Protection class IP 65
- IP Protection Classes → page QVX
- Stainless Steel Characteristics → page QVX
- RoHS

Accessory

- Protective Guide Plates GN 120.2 → page QVX
- Internal Cabinet Handles GN 120.3 → page QVX
- Sheet Metal Punches GN 123 → page QVX

Information

Cam latches GN 115 lock by a turning operation limited to 90° which moves the latch arm in the locked position behind the door frame. The bevels of the latch arm ease the closing of the door. Thanks to the stainless steel materials used, the latches are optimally suited for use in corrosive environments.

Latch arms are available with different bend angles to cover a latch arm distance A from 6 to 28 mm. Product comes supplied with a loosely enclosed latch arm.

see also...

- Construction and Assembly Instructions → page QVX
- List of Cam Latch / Cam Lock Types → page QVX
- Cam Latches GN 115 (Zinc Die-Cast, Operation with Socket Key) → page QVX
- Cam Latches GN 115 (Stainless Steel, with Stainless Steel Operating Elements) → page QVX
- Cam Latches GN 115 (Stainless Steel, with Plastic Operating Elements) → page QVX
- Cam Latches GN 115 (Stainless Steel, Operation with Socket Keys, Protection Class IP 69k) → page QVX
- Cam Locks GN 115 (Stainless Steel) → page QVX

How to order

GN 115-SKN-10-A4

1	Type
2	Latch arm distance A
3	Material