



Metric table

Dimensions in: millimeters - inches

¹ l ₁	² d ₁ Thread	² d ₂ Bore	b ₁	b ₂	b ₃	h ₁	h ₂	l ₂ ±0.5	l ₃	t ₁	t ₂
108 4.25	M 5	B 4.5	60 2.36	26.5 1.04	11 0.43	20.5 0.81	17.5 0.69	71 2.80	91 3.58	12 0.47	15.5 0.61

Specification

- Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 212 °F (100 °C)
- Black-gray, RAL 7021, matte finish ● **SG**
- Tapped inserts
Brass
- *Strength Properties* → page QVX
- *Plastic Characteristics* → page QVX
- **RoHS compliant**

Information

EN 130.3 ledge handles with bore hole B 4.5 are intended for mounting with self-tapping screws of thread size ST 4.8 such as DIN ISO 7049 pan head self-tapping screw.

see also...

- *Ledge Handles EN 130.2 (Technopolymer Plastic)* → page QVX
- *Ledge Handles GN 730 (Aluminum)* → page QVX
- *Ledge Handles GN 430 (Aluminum)* → page QVX

How to order

EN 130.3-108-B4.5-SG

¹	Length l ₁
²	Thread d ₁ (Bore d ₂)
³	Color