




Metric table

1 s₁	2 s₂	3 n	6 Length l +1.5mm in meters	7 Bundle Pieces	d	k	s₃	t	Grid size
30 1.18	30 1.18	6 0.24	2	4	5 0.20	-	3 0.12	9.75 0.38	30 1.18
30 1.18	60 2.36	6 0.24	2	2	5 0.20	30 1.18	3 0.12	9.75 0.38	30 1.18
40 1.57	40 1.57	8 0.31	2	4	6.8 0.27	-	4.5 0.18	12.25 0.48	40 1.57
40 1.57	80 3.15	8 0.31	2	2	6.8 0.27	40 1.57	4.5 0.18	12.25 0.48	40 1.57
60 2.36	60 2.36	6 0.24	2	1	5 0.20	30 1.18	3 0.12	9.75 0.38	30 1.18
80 3.15	80 3.15	8 0.31	2	1	6.8 0.27	40 1.57	4.5 0.18	12.25 0.48	40 1.57

Specification

- Aluminum

Anodized finish, natural color

5

N
- RoHS

Accessory

- T-nuts GN 50i → page QVX
- Cover caps GN 60i → page QVX
- Cover and edging profiles GN 70i → page QVX
- Cover profiles GN 71i → page QVX
- Support / base plates GN 80i → page QVX

Information

Aluminum profiles GN 10i are produced by extrusion molding. They can be used, for example, to easily construct protective enclosures, workplace equipment or jigs.

Aluminum profiles in combination with the removable and reusable accessories form a flexible modular system. Attachments can be fastened to either the slots or the end faces via the holes.

The profile type light is typically used for small loads or for weight-optimized constructions.

Aluminum profiles are supplied in bundles. The table shows the quantity included in each bundle.

How to order	1 Profile width s ₁
	2 Profile height s ₂
	3 Slot width n
	4 Profile type
	5 Finish
	6 Length l (in meters)
	7 Bundle

1

2

3

4

5

6

7

GN 10i-40 40 8 L-N-2-4