













Metric



SS Stainless Steel

1 Type

RG With hollow knurled knob GN 7336

KG With wing knob

HG With lever

3 Hook version

H1 Pivoting radius R=28mm

5 Identification no.

1 Without latch bracket

2 With latch bracket

Metric table

2

Dimensions in: millimeters / inches		
Hook distance A	d	h
18 0.71	28 1.10	4 0.16

* Dimensions of the latch bracket, see page XYZ

Specification	4
Cam latch housing	N
Stainless steel AISI 303	
Operating elements	
Plastic, Polyamide (PA)	
Black, matte finish	
Other parts	
Stainless steel AISI 304	
Cover cap	
Plastic	
Light gray, matte finish	
Protection class IP 65	
RoHS	
On request	
• Cam latches with other hook distance A	
• Hook with other pivoting radius R	

Cam latches with hook GN 115.8 and latch bracket are mainly used for sliding doors and flaps. The latching action is in a radial direction to the axis of rotation, resulting in a wide variety of different uses. The latches GN 115.8 are supplied with loosely enclosed hook.

see also...	Page
GN 115.8 Cam Latches with Hook (Stainless Steel, with Operating Elements)	QVX
GN 115.8 Cam Latches with Hook (Stainless Steel, Operation with Socket Key)	QVX
GN 115.8 Cam Locks with Hook (Stainless Steel)	QVX

Technical Information	
Construction and Assembly Instructions	QVX
List of Cam Latch / Cam Lock Types	QVX
IP Protection Classes	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order	1 Type
GN 115.8-RG-18-H1-N-2	2 Hook distance A
	3 Hook version
	4 Werkstoff
	5 Identification no.