



3 Type

- A** Mounting with countersunk screw
- B** Mounting with adhesive pad

Metric table

Dimensions in: millimeters - inches

1 h	2 b ₁	b ₂	d ₁ Thread	d ₂	l ₁	l ₂	m ₁	m ₂ ±2	Usable for
60 2.36	4 0.16	4.6 0.18	M 4	3 0.12	20 0.79	10 0.39	40 1.57	35 1.38	GN 115 / GN 115.7 / GN 115.9 / GN 115.10 / GN 515

Specification

- Guide plate
Plastic
Technopolymer (Polyamide PA)
Black, matte finish **SW**
- Adhesive pad (only Type B)
Scotch-Mount™ 4026
Double-sided, with polyurethane foam backing
- *Plastic Characteristics* → page QVX
- **RoHS compliant**

Information

GN 120.2 protective guide plates are used in connection with cam door latches, using the principle of friction. They prevent the latch arm from causing abrasion, for example, to the corrosion protection layers on a door frame. They additionally prevent unintended opening, as the latch arms lock into a small recess in their closed position.

If the d₂ positioning tabs are not required they can easily be removed with side cutting pliers.

see also...

- *List of Cam Latch / Cam Lock Types* → page XYZ
- *Protective Caps GN 120* → page XYZ
- *Finger Grip Opening Handles GN 120.1* → page XYZ

How to order

GN 120.2-60-4-A-SW

1	Height h
2	Width b ₁
3	Type
4	Color