



Type H



Type B



Type HB



elisa  
Original design CFA/SL



3 Type

- H Vertical slots
- B Horizontal slots
- HB Horizontal and vertical slots

Metric table

Dimensions in: millimeters - inches

1	2											
$l_1$	$l_2$	$d_1$	$d_2$	$h_1$	$h_2$	$h_3$	$h_4$	$l_3$	$m_1$	$m_2$	$t$	
64	65	6.5	5	23	13.5	15	30	24	40	40	6.5	
2.52	2.56	0.26	0.20	0.91	0.53	0.59	1.18	0.94	1.57	1.57	0.26	

Specification

- Body  
Plastic  
Technopolymer (Polyamide PA)  
- Black, matte finish  
- Temperature resistant up to 176 °F (80 °C)
- Pin  
Stainless steel AISI 303
- Load Rating Information → page 2095
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

EN 151.4 hinges are adjustable vertically or horizontally along the slots and are fastened with cylinder head screws.

see also...

- Product Family Standard Parts for Profile Systems → page 18
- List of Hinge Types → page 1324
- Adjustable Alignment Hinges GN 127 (Zinc Die-Cast) → page 1404
- Hinges EN 236 (Technopolymer Plastic, Adjustable) → www.jwwinco.com
- Adjustable Alignment Hinges GN 238 (Zinc Die-Cast) → page 1402
- T-Nut Assemblies GN 965 (for 30 / 40 Aluminum T-Slot Profile Systems) → page 2048
- T-Nut Assemblies GN 968 (for 30 / 40 / 45 Aluminum T-Slot Profile Systems) → page 2058

How to order

EN 151.4-64-65-HB

1	Width $l_1$
2	Length $l_2$
3	Type