



- Type**
- D Straight lever
 - E Angled lever

Inch table

Dimensions in: inches - millimeters

d ₁	d ₂		d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄ ≈	h ₅ Stroke	Length l	t min.
1.26 32	1/4 x 20	5/16 x 18	0.53 13.5	0.31 8	0.79 20	0.81 20.5	0.06 1.5	0.49 12.5	1.42 36	0.16 4	3.94 100	0.43 11
1.42 36	5/16 x 18	3/8 x 16	0.63 16	0.39 10	0.98 25	0.96 24.5	0.08 2	0.59 15	1.77 45	0.18 4.5	4.72 120	0.55 14
1.57 40	3/8 x 16	1/2 x 13	0.75 19	0.47 12	1.18 30	1.04 26.5	0.08 2	0.63 16	1.97 50	0.18 4.5	5.12 130	0.67 17
1.77 45	1/2 x 13	5/8 x 11	0.91 23	0.47 12	1.26 32	1.24 31.5	0.08 2	0.79 20	2.36 60	0.20 5	5.71 145	0.91 23

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂		d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄ ≈	h ₅ Stroke	Length l	t min.	
32 1.26	M 6	M 8	-	13.5 0.53	8 0.31	20 0.79	20.5 0.81	1.5 0.06	12.5 0.49	36 1.42	4 0.16	100 3.94	11 0.43
36 1.42	M 8	M 10	M 12	16 0.63	10 0.39	25 0.98	24.5 0.96	2 0.08	15 0.59	45 1.77	4.5 0.18	120 4.72	14 0.55
40 1.57	M 10	M 12	-	19 0.75	12 0.47	30 1.18	26.5 1.04	2 0.08	16 0.63	50 1.97	4.5 0.18	130 5.12	17 0.67
45 1.77	M 12	M 14	M 16	23 0.91	12 0.47	32 1.26	31.5 1.24	2 0.08	20 0.79	60 2.36	5 0.20	145 5.71	23 0.91

Specification

- Body / lever / insert
Steel, blackened finish
- Cover
Plastic, light gray
- Ball knob DIN 319 → page 55
Plastic
Duroplast (Phenolic PF)
Black, shiny finish
- Safety circlip
Plastic (Polyacetal POM)
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Special plain blind bores, through bores, threads and threaded through bores

Information

With the GN 125 flat adjustable tension levers, the overall height is reduced to a minimum. The cover disk gives these levers a nice appearance.

As all other adjustable levers, they are ideal wherever parts have to be clamped in a confined space or in a particular lever position. The threaded insert is connected with the hub via serrations that can be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

How to order (Inch)	
1	Diameter d ₁
2	Thread d ₂
3	Type

GN 125-32-1/4X20-D

How to order (Metric)	
1	Diameter d ₁
2	Thread d ₂
3	Type

GN 125-40-M12-E