



- 4 Identification no.**
2 With 2 stainless steel socket cap screws DIN 912

Dimensions in: millimeters - inches

1 d ₁ Bore	2 d ₂ Bore	3 k ₁ Clamping length	k ₂ Clamping length	l ₁	l ₂	l ₃	m	z Screw locations for screw size	Accessory Recommended levers GN 911.9 for z l ₄	
B 18	B 18	29 1.14	30.5 1.20	65 2.56	34 1.34	29 1.14	43.5 1.71	M6-18	44 1.73	63 2.48
B 30	B 30	44 1.73	45.5 1.79	96 3.78	53 2.09	44 1.73	64.5 2.54	M8-25	63 2.48	78 3.07

Specification

- Body
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 212 °F (100 °C)
- Black, RAL 9005, matte finish **S**
- Gray, RAL 7040, matte finish **G**
- Blue, RAL 5005, matte finish **V**
FDA compliant plastic granulate
Visually detectable
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
- Stainless steel AISI 304
- Self-locking with polyamide ring
- Load Rating Information → page QVX
- Plastic Characteristics → page QVX
- Stainless Steel Characteristics → page QVX
- RoHS compliant

Accessory

- Adapter bushings EN 290 → page QVX
- Adjustable levers GN 911.9 → page QVX

Information

The clamping bores axes of the T-angle connector clamps EN 192.9 lie in the same plane, arranged in a T-shape. They hold typical construction tubes with full surface contact over the entire cross-section of the bore.

At the screw locations z, the socket cap screws reduce the bore cross-section for clamping. Adapter bushings EN 290 can be used to reduce the bore cross-sections to a smaller diameter.

For clamping without tools, the socket cap screws can be replaced by the adjustable levers GN 911.9 listed in the table as accessories.

The plastic used in version V is made from blue, visually detectable and FDA compliant plastic granulate as per FDA CFR.21 and EU 10/2011.

see also...

- Construction Tubes GN 990 → page QVX

How to order	
1	Bore d ₁
2	Bore d ₂
3	Clamping length k ₁
4	Identification no.
5	Color

EN 192.9-B30-B30-44-2-S