


Metric



elesa
Original design MLP



Metric table

Dimensions in: millimeters / inches

¹ l ₁	² d ₁	² d ₂	b ₁	b ₂	b ₃	h ₁	h ₂	l ₂	l ₃	t ₁	t ₂
120 4.72	M 4	B 4.5	22 0.87	19.5 0.77	8 0.31	21 0.83	18 0.71	142 5.59	107 4.21	10 0.39	13 0.51

Specification

Handle

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature
-22 °F to +212 °F (-30 °C to +100 °C)
- Black-gray, RAL 7021, matte finish ● **SG**

Tapped inserts

Brass

RoHS

Ledge handles EN 130.2 with bore hole B 4.5 are intended for mounting with self-tapping screws of thread size ST 4.8 such as pan head self-tapping screw DIN ISO 7049.

see also...	Page
EN 130 Ledge Handles	QVX
GN 730 Ledge Handles (Aluminum)	QVX
GN 430 Ledge Handles (Aluminum)	QVX

Technical Information

Strength Values	QVX
Plastic Characteristics	QVX

How to order

EN 130.2-120-M4-SG

¹	Length l ₁
²	Thread d ₁ (Bore d ₂)
³	Color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

