



- 3 Type**
- N Angled lever with tapped bore
  - L Angled lever with plain bore

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub>	<b>2</b> d <sub>2</sub> Thread	<b>2</b> d <sub>3</sub> H7 Bore	b	d <sub>4</sub> ≈	d <sub>5</sub>	h ≈	l <sub>1</sub>	l <sub>2</sub> ≈
10 0.39	M 8	-	11 0.43	12.5 0.49	16 0.63	26 1.02	50 1.97	48 1.89
13 0.51	M 10	B 10	14 0.55	16 0.63	20 0.79	32 1.26	63 2.48	60 2.36
16 0.63	M 12	B 12	17.5 0.69	20 0.79	25 0.98	40 1.57	80 3.15	76 2.99
20 0.79	M 16	B 16	23 0.91	25 0.98	32 1.26	51 2.01	100 3.94	95 3.74
25 0.98	M 20	-	30 1.18	31 1.22	40 1.57	63.5 2.50	125 4.92	119 4.69

**Specification**

- Body  
Steel
- Turned
- Blackened finish
- ISO Fundamental Tolerances → page QVX
- RoHS compliant

**On request**

- Short clamping levers with straight lever
- Special inch and metric bores or threads

**Information**

GN 204 fixed clamping levers are machined from solid bar and are the shortened version of the DIN 99 clamping levers. Ideal for smaller, more confined applications.

How to order <b>GN 204-16-M12-N</b>	<b>1</b> Diameter d <sub>1</sub>
	<b>2</b> Thread d <sub>2</sub> (Bore d <sub>3</sub> )
	<b>3</b> Type