


Metric



SS Stainless Steel

3 Identification no.

2 With 3 socket cap screws
ISO 4762

Metric table

Dimensions in: millimeters / inches									
d ₁	d ₂	k	l ₁	l ₂	m	s ₁ Square	s ₂ Square	z ₁ Screw location	z ₂ Screw location
B 12	B 12	12 0.47	36.5 1.44	25 0.98	14 0.55	10	10	M4-12	M4-12
B 20	B 12	20 0.79	51 2.01	42 1.65	20 0.79	16	10	M6-20	M6-12
B 20	B 20	20 0.79	57 2.24	42 1.65	22 0.87	16	16	M6-20	M6-18

Specification

Connector clamp

Stainless steel AISI CF-8
Matte shot-blasted finish

NI

Socket cap screws ISO 4762

Stainless steel AISI 304

RoHS

The clamping bores of the two-way connector clamps GN 131.3 are designed for typical construction tubes. The square sections s₁ and s₂ also allow bars or tubes with a square cross-section to be clamped.

At the screw locations z₁ and z₂, socket cap screws reduce the bore cross-section for clamping. The split clamping point z₂ allows the connector clamp to be subsequently inserted into an existing structure and facilitates assembly when axial sliding is not possible, e.g., due to tight bending radii.

see also...

Page

GN 131 Two-Way Connector Clamps (Aluminum / Stainless Steel, Single Part) QVX

GN 474 Two-Way Mounting Clamps (Aluminum, Single Part) QVX

GN 131.4 Two-Way Connector Clamps QVX

Technical Information

Stainless Steel Characteristics QVX

Accessory

GN 990 Construction Tubes QVX

How to order

GN 131.3-B20-B12-2-NI

1 Bore d₁

2 Bore d₂

3 Identification no.

4 Material