



Application example



**Metric table**

Dimensions in: millimeters - *inches*

<sup>1</sup> d <sub>1</sub> Thread	<sup>2</sup> Length l	d <sub>2</sub>	d <sub>3</sub>	A/F	t <sub>1</sub>	t <sub>2</sub>
M 12	56 2.20	25 0.98	25.8 1.02	19 0.75	15.5 0.61	50 1.97
M 16	62 2.44	28 1.10	28.8 1.13	22 0.87	20.5 0.81	55 2.17
M 20	68 2.68	32 1.26	32.8 1.29	27 1.06	25.5 1.00	60 2.36
M 24	74 2.91	36 1.42	36.8 1.45	30 1.18	30.5 1.20	65 2.56

**Specification**

- Body  
Stainless steel AISI 304
- Sealing ring
  - H-NBR **H**  
Temperature resistant from -13 °F to +302 °F (-25 °C to +150 °C)
  - EPDM **E**  
Temperature resistant from -40 °F to +248 °F (-40 °C to +120 °C)
  - Blue
  - Hardness 85 ±5 shore A
  - FDA compliant
- 3-A and EHEDG Principles → page XYZ
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

**Accessory**

- Sealing rings GN 7600 → page 1683

**Information**

GN 20.1 protective end caps comply with the guidelines of the EHEDG, the 3-A sanitary standard 88-01 and the DGVU testing principles, making them extremely suitable for use in hygienic areas.

They cover protruding threaded studs and at the same time they replace lock nuts. The sealed mounting surface enables fastening without dead spaces. The high surface quality prevents adherence of dirt and facilitates cleaning.

see also...

- Product Family [Hygienic Design](#) → page 16
- Leveling Feet GN 20 (Stainless Steel, [Hygienic Design](#)) → page 1505 / 1506
- Leveling Feet GN 19 (Stainless Steel, [Hygienic Design](#)) → page XYZ

How to order

**GN 20.1-M12-56-H**

- <sup>1</sup> Thread d<sub>1</sub>
- <sup>2</sup> Length l
- <sup>3</sup> Sealing ring material