


Metric



SS Stainless Steel

3 Identification no.

2 With 3 socket cap screws ISO 4762

Metric table

Dimensions in: millimeters / inches									
1 d ₁	2 d ₂	k	l ₁	l ₂	m	s ₁ Square	s ₂ Square	z ₁ Screw location	z ₂ Screw location
B 12	B 12	20 0.79	35.5 1.40	42 1.65	14 0.55	10	10	M6-8	M6-12
B 12	B 20	20 0.79	44.5 1.75	42 1.65	17 0.67	10	16	M6-10	M6-18

Specification

Connector clamp

Stainless steel AISI CF-8
Matte shot-blasted finish

4

NI

Socket cap screws ISO 4762

Stainless steel AISI 304

RoHS

The clamping bores of the two-way connector clamps GN 131.4 are designed for typical construction tubes. The square sections s₁ and s₂ also allow bars or tubes with a square cross-section to be clamped. Clamping at screw point z₁ is performed radially on the surface of the profiles used. At the screw location z₂, socket cap screws reduce the bore cross-section for clamping. The split clamping point z₂ permits subsequent insertion of the clamp connector into an existing structure and facilitates assembly when axial sliding is not possible, e.g., due to tight bending radii.

see also...

Page

GN 131 Two-Way Connector Clamps (Aluminum / Stainless Steel, Single Part)	QVX
GN 474 Two-Way Mounting Clamps (Aluminum, Single Part)	QVX
GN 131.3 Two-Way Connector Clamps	QVX

Technical Information

Stainless Steel Characteristics	QVX
---------------------------------	-----

Accessory

GN 990 Construction Tubes	QVX
----------------------------------	-----

How to order

GN 131.4-B12-B12-2-NI

- 1** Bore d₁
- 2** Bore d₂
- 3** Identification no.
- 4** Material