



- 4 Identification no.**
- 2** With 2 stainless steel socket cap screws DIN 912

Specification

- Body
Aluminum
- Powder coated
Black, RAL 9005, textured finish ● **SW**
- Plain, matte shot-blasted finish ○ **BL**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
Stainless steel AISI 304
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

5

Information

The clamping bores of GN 132 two-way connector clamps are mechanically machined and designed for GN 990 or DIN 2391, DIN 2395 and DIN 2462 construction tubes.

At the screw locations **z**, the socket cap screws reduce the bore cross-section for clamping.

For clamping without tools, the socket cap screws can be replaced by the GN 911 adjustable levers listed in the table as accessories.

see also...

- *Construction Tubes GN 990* → page 1836
- *Two-Way Linear Actuator Connectors GN 132.1 / GN 132.2* → page 1949

Accessory

- Adjustable levers GN 911 → page 1810

On request

- d_1 / d_2 with unequal bores

How to order	
1	Bore d_1
2	Bore d_2
3	Clamping length k
4	Identification no.
5	Finish

GN 132-B1.00-B1.00-40-2-BL

Inch table

Dimensions in: inches - *millimeters*

1 d ₁ Bore	2 d ₂ Bore	3 k Clamping length	l ₁	l ₂	m	z Screw locations for screw size	Accessory Recommended lever GN 911 for z l ₃	
B 1.00	B 1.00	1.57 40	3.82 97	1.57 40	1.30 33	M8-25	63 2.48	78 3.07
B 1 1/4	B 1 1/4	2.20 56	4.92 125	2.20 56	1.77 45	M10-35	-	-
B 1 1/2	B 1 1/2	2.20 56	4.92 125	2.20 56	1.77 45	M10-35	78 3.07	92 3.62
B 1 3/4	B 1 3/4	2.56 65	5.63 143	2.56 65	2.09 53	M10-50	78 3.07	92 3.62
B 2.00	B 2.00	2.56 65	5.63 143	2.56 65	2.09 53	M10-50	78 3.07	92 3.62
B 2 1/2	B 2 1/2	3.15 80	6.65 169	3.15 80	2.56 65	M10-50	78 3.07	92 3.62

Metric table

Dimensions in: millimeters - *inches*

1 d ₁ Bore	2 d ₂ Bore	3 k Clamping length	l ₁	l ₂	m	z Screw locations for screw size	Accessory Recommended lever GN 911 for z l ₃	
B 20	B 20	40 1.57	97 3.82	40 1.57	33 1.30	M8-25	-	-
B 25	B 25	40 1.57	97 3.82	40 1.57	33 1.30	M8-25	63 2.48	78 3.07
B 30	B 30	40 1.57	97 3.82	40 1.57	33 1.30	M8-25	63 2.48	78 3.07
B 30	B 30	56 2.20	125 4.92	56 2.20	45 1.77	M10-35	-	-
B 32	B 32	56 2.20	125 4.92	56 2.20	45 1.77	M10-35	-	-
B 35	B 35	56 2.20	125 4.92	56 2.20	45 1.77	M10-35	78 3.07	92 3.62
B 40	B 40	56 2.20	125 4.92	56 2.20	45 1.77	M10-35	78 3.07	92 3.62
B 40	B 40	65 2.56	143 5.63	65 2.56	53 2.09	M10-50	-	-
B 42	B 42	65 2.56	143 5.63	65 2.56	53 2.09	M10-50	78 3.07	92 3.62
B 45	B 45	65 2.56	143 5.63	65 2.56	53 2.09	M10-50	78 3.07	92 3.62
B 48	B 48	65 2.56	143 5.63	65 2.56	53 2.09	M10-50	78 3.07	92 3.62
B 50	B 50	65 2.56	143 5.63	65 2.56	53 2.09	M10-50	78 3.07	92 3.62
B 50	B 50	80 3.15	169 6.65	80 3.15	65 2.56	M10-50	-	-
B 60	B 60	80 3.15	169 6.65	80 3.15	65 2.56	M10-50	78 3.07	92 3.62

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

