



SS Stainless Steel

**4 Type**

- A Without bores
- B With through holes
- C With countersunk holes

**Metric table**

Dimensions in: millimeters - inches

2		3										
$l_1$		$l_2$	$d_1$	$d_2$	$d_3$	$d_4$	$m_1$	$m_2$	$m_4$	$m_5$	$s$	
Extended on one side	Extended on both sides											
45 1.77	-	30 1.18	3 0.12	3.2 0.13	4 0.16	6.4 0.25	33 1.30	18 0.71	9 0.35	24 0.94	1.5 0.06	
-	60 2.36	30 1.18	3 0.12	3.2 0.13	4 0.16	6.4 0.25	48 1.89	18 0.71	9 0.35	24 0.94	1.5 0.06	
60 2.36	-	40 1.57	4 0.16	4.2 0.17	5 0.20	8.3 0.33	45 1.77	25 0.98	12.5 0.49	32.5 1.28	2 0.08	
-	80 3.15	40 1.57	4 0.16	4.2 0.17	5 0.20	8.3 0.33	65 2.56	25 0.98	12.5 0.49	32.5 1.28	2 0.08	
75 2.95	-	50 1.97	6 0.24	5.2 0.20	5 0.20	8.3 0.33	55 2.17	30 1.18	15 0.59	40 1.57	2 0.08	
-	100 3.94	50 1.97	6 0.24	5.2 0.20	5 0.20	8.3 0.33	80 3.15	30 1.18	15 0.59	40 1.57	2 0.08	
90 3.54	-	60 2.36	6 0.24	5.2 0.20	5 0.20	8.3 0.33	66 2.60	36 1.42	18 0.71	48 1.89	2 0.08	
-	120 4.72	60 2.36	6 0.24	5.2 0.20	5 0.20	8.3 0.33	96 3.78	36 1.42	18 0.71	48 1.89	2 0.08	

**Specification**

- Body
  - Steel, zinc plated, blue passivated finish **ST**
  - (Only Type B and C)
  - Stainless steel AISI 304 **NI**
- Pin
  - Stainless steel AISI 304
  - Riveted
- Load Rating Information → page 2088
- Stainless Steel Characteristics → page 2143
- RoHS compliant

**Information**

GN 136 sheet metal hinges are available in many different versions and are suitable for light to medium-duty applications.

Type A can be assembled by welding or done via custom made holes in the hinge.

see also...

- List of Hinge Types → page 1324
- Sheet Metal Hinges GN 1362 (Stainless Steel, Weldable) → page 1340
- Sheet Metal Hinges GN 1364 (Stainless Steel) → page 1341
- Hinges GN 1366 (Steel Profile, Weldable) → page 1342

How to order	
1	Material
2	Width $l_1$
3	Length $l_2$
4	Type

**GN 136-ST-60-40-B**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10