



3 Type
E Angled lever
D Straight lever

Inch table

Dimensions in: inches - millimeters

d ₁	d ₂		d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄ ≈		h ₅ Stroke	l ₂ ≈		l ₃ ≈	t min.
									Type E	Type D		Type E	Type D		
0.83 21	1/4 x 20	5/16 x 18	0.53 13.5	0.31 8	0.79 20	1.32 33.5	1.22 31	0.04 1	2.32 59	1.42 36	0.16 4	2.95 75	3.17 80.5	2.76 70	0.43 11
0.94 24	5/16 x 18	3/8 x 16	0.63 16	0.39 10	0.98 25	1.57 40	1.46 37	0.10 2.5	2.95 75	1.71 43.5	0.18 4.5	3.98 101	4.25 108	3.78 96	0.55 14
1.10 28	3/8 x 16	1/2 x 13	0.75 19	0.47 12	1.18 30	1.91 48.5	1.75 44.5	0.18 4.5	3.50 89	2.07 52.5	0.18 4.5	4.57 116	4.88 124	4.33 110	0.67 17
1.30 33	1/2 x 13	5/8 x 11	0.91 23	0.47 12	1.26 32	2.17 55	2.03 51.5	0.24 6	3.96 100.5	2.36 60	0.22 5.5	5.18 131.5	5.53 140.5	4.88 124	0.87 22
1.57 40	3/4 x 10	-	1.10 28	0.55 14	1.38 35	2.68 68	2.52 64	0.24 6	4.65 118	2.81 71.5	0.22 5.5	5.83 148	6.22 158	5.43 138	1.42 36

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂		d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄ ≈		h ₅ Stroke	l ₂ ≈		l ₃ ≈	t min.	
									Type E	Type D		Type E	Type D			
21 0.83	M 6	M 8	-	13.5 0.53	8 0.31	20 0.79	33.5 1.32	31 1.22	1 0.04	59 2.32	36 1.42	4 0.16	75 2.95	80.5 3.17	70 2.76	11 0.43
24 0.94	M 8	M 10	-	16 0.63	10 0.39	25 0.98	40 1.57	37 1.46	2.5 0.10	75 2.95	43.5 1.71	4.5 0.18	101 3.98	108 4.25	96 3.78	14 0.55
28 1.10	M 10	M 12	-	19 0.75	12 0.47	30 1.18	48.5 1.91	44.5 1.75	4.5 0.18	89 3.50	52.5 2.07	4.5 0.18	116 4.57	124 4.88	110 4.33	17 0.67
33 1.30	M 12	M 14	M 16	23 0.91	12 0.47	32 1.26	55 2.17	51.5 2.03	6 0.24	100.5 3.96	60 2.36	5.5 0.22	131.5 5.18	140.5 5.53	124 4.88	22 0.87
40 1.57	M 16	M 20	-	28 1.10	14 0.55	35 1.38	68 2.68	64 2.52	6 0.24	118 4.65	71.5 2.81	5.5 0.22	148 5.83	158 6.22	138 5.43	36 1.42

Specification

- Body / lever / insert
Steel, blackened finish
- Ball knob DIN 319 → page 55
Plastic
Duroplast (Phenolic PF)
Black, shiny finish
- Safety circlip
Plastic (Polyacetal POM)
- Plastic Characteristics → page 2135
- RoHS compliant

Information

GN 212.3 heavy duty adjustable levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The threaded insert is connected with the hub via serrations that can be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

How to order (Inch) 1 Diameter d ₁ 2 Thread d ₂ 3 Type GN 212.3-21-1/4X20-D	1	Diameter d ₁
	2	Thread d ₂
	3	Type
How to order (Metric) 1 Diameter d ₁ 2 Thread d ₂ 3 Type GN 212.3-28-M12-E	1	Diameter d ₁
	2	Thread d ₂
	3	Type