



- 2 Bore code**
- B** Without keyway
 - K** With keyway
 - V** With square

Metric table

Dimensions in: millimeters - inches

1 d ₁	3 d ₂ Bore H7 Square H11	d ₃	d ₄	d ₅	h ₁	h ₂	h ₃ ≈	Length l ≈
50 1.97	12 0.472	28 1.10	8 0.31	20 0.79	26 1.02	9 0.35	53 2.09	82 3.23
55 2.17	14 0.551	30 1.18	10 0.39	25 0.98	28 1.10	10 0.39	61 2.40	96 3.78
60 2.36	15 0.591	32 1.26	10 0.39	25 0.98	30 1.18	11 0.43	64 2.52	96 3.78
65 2.56	16 0.630	35 1.38	12 0.47	30 1.18	32 1.26	12 0.47	71 2.80	110 4.33
72 2.83	18 0.709	40 1.57	12 0.47	32 1.26	36 1.42	14 0.55	80 3.15	124 4.88
80 3.15	20 0.787	44 1.73	14 0.55	35 1.38	40 1.57	16 0.63	89 3.50	138 5.43
100 3.94	24 0.945	54 2.13	16 0.63	40 1.57	52 2.05	24 0.94	113 4.45	170 6.69

Specification

- Hub / arms
Steel, blackened finish
- Ball knob DIN 319 → page 55
Plastic
Duroplast (Phenolic PF)
Black, shiny finish
- Keyways WN / DIN 6885 → page 2040
- ISO Fundamental Tolerances → page 2129
- Plastic Characteristics → page 2135
- RoHS compliant

On request

- Special inch and metric bores, threads or keyways
- Other modifications such as set screw holes, cross holes, etc.

Information

GN 213 four arm turret levers are an excellent choice for applications where using a handwheel or crank handle is not practical.

<p>How to order</p> <p>GN213-65-B16</p>	1 Diameter d ₁
	2 Bore code
	3 Bore d ₂ (Keyway, Square)