



Metric table

Dimensions in: millimeters - inches

d	s ₀	s ₁ ±0.1	s ₂ ±0.1	l ₁ ±0.5	l ₂	No. of spokes
50 1.97	V 6	5.9 0.23	6.15 0.24	8.5 0.33	12 0.47	3
50 1.97	V 7	6.9 0.27	7.15 0.28	8.5 0.33	12 0.47	3
60 2.36	V 6	5.9 0.23	6.15 0.24	8.5 0.33	12 0.47	3
60 2.36	V 7	6.9 0.27	7.15 0.28	8.5 0.33	12 0.47	3
70 2.76	V 7	6.9 0.27	7.15 0.28	10 0.39	15 0.59	3
70 2.76	V 8	7.9 0.31	8.15 0.32	10 0.39	15 0.59	3
80 3.15	V 8	7.9 0.31	8.15 0.32	11 0.43	16 0.63	3
80 3.15	V 9	8.9 0.35	9.15 0.36	11 0.43	16 0.63	3
90 3.54	V 9	8.9 0.35	9.15 0.36	11 0.43	16 0.63	3
100 3.94	V 9	8.9 0.35	9.15 0.36	13 0.51	20 0.79	3
100 3.94	V 10	9.9 0.39	10.15 0.40	13 0.51	20 0.79	3
130 5.12	V 12	11.9 0.47	12.15 0.48	15 0.59	23 0.91	3

Specification

- Steel sheet metal **ST**
- Powder coated
 - Black, RAL 9005, matte finish
 - Red, RAL 3000, matte finish
 - Zinc plated, blue passivated finish
- RoHS compliant



- **SW**
- **RT**
- **ZB**

Information

GN 227.6 valve handwheels have been specially developed for valves and they offer definite advantages: They consist of **a single** unwelded piece of steel sheet metal manufactured by a special process to give a reinforced hub. They offer high mechanical strength and are not affected by shocks and knocks. They are resistant to temperature and fire and not weakened by any aging process. The slightly tapered square hole allows easy installation and firm seating on a spindle. They are of an attractive design and low cost.

How to order	
1	Material
2	Handwheel diameter d
3	Square s ₀
4	Finish

GN 227.6-ST-60-V7-SW

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4