



Definitions

F_1 = Static load in vertical direction (pressure)

F_2 = Static load in horizontal direction (lateral thrust)

s_1 = Compression in vertical direction (spring excursion) under load through F_1

s_2 = Compression in vertical direction (spring excursion) under load through F_2

Stiffness R:

Is the load that causes the damping pad to be compressed by 1 in / 1 mm (spring rate)

Equation for calculating the stiffness: $R = \frac{F}{s}$

The table below gives details on the maximum static load F, the maximum permissible compression and the resulting stiffness R.

The method shown on page 1567 and the values given below allow the maximum degree of insulation of the vibration to be determined as a factor of the interference frequency.

Dimensions in: millimeters - inches

d_1	Hardness in shore	Max. static load F_1	Stiffness R_1	Max. compression s_1	Max. static load F_2	Stiffness R_2	Max. compression s_2
60 2.36	43	1100 N 247 lbf	340 N/mm 1945 lbf/in	3.2 0.13	2300 N 517 lbf	770 N/mm 4405 lbf/in	3 0.12
60 2.36	57	1750 N 393 lbf	550 N/mm 3146 lbf/in	3.2 0.13	3400 N 764 lbf	1130 N/mm 6464 lbf/in	3 0.12
60 2.36	68	2800 N 630 lbf	930 N/mm 5320 lbf/in	3 0.12	4000 N 899 lbf	1330 N/mm 7609 lbf/in	3 0.12
90 3.54	43	1500 N 337 lbf	430 N/mm 2460 lbf/in	3.5 0.14	3000 N 674 lbf	750 N/mm 4291 lbf/in	4 0.16
90 3.54	57	2800 N 630 lbf	800 N/mm 4577 lbf/in	3.5 0.14	5000 N 1124 lbf	1330 N/mm 7609 lbf/in	3.75 0.14
90 3.54	68	4500 N 1012 lbf	1290 N/mm 7380 lbf/in	3.5 0.14	7000 N 1574 lbf	1870 N/mm 10698 lbf/in	3.75 0.14
113 4.45	43	3500 N 787 lbf	1000 N/mm 5721 lbf/in	3.5 0.14	4500 N 1012 lbf	1290 N/mm 7380 lbf/in	3.5 0.14
113 4.45	57	6500 N 1461 lbf	1860 N/mm 10641 lbf/in	3.5 0.14	7500 N 1686 lbf	2140 N/mm 12242 lbf/in	3.5 0.14
113 4.45	68	10000 N 2248 lbf	2860 N/mm 16361 lbf/in	3.5 0.14	11000 N 2473 lbf	3140 N/mm 17963 lbf/in	3.5 0.14
126 4.96	43	7500 N 1686 lbf	2140 N/mm 12242 lbf/in	3.5 0.14	9000 N 2023 lbf	2570 N/mm 14702 lbf/in	3.5 0.14
126 4.96	57	12500 N 2810 lbf	3570 N/mm 20423 lbf/in	3.5 0.14	15000 N 3372 lbf	4290 N/mm 24542 lbf/in	3.5 0.14
126 4.96	68	19000 N 4271 lbf	5340 N/mm 30549 lbf/in	3.5 0.14	22500 N 5058 lbf	6430 N/mm 36784 lbf/in	3.5 0.14

Application example

