





Assembly / profile machining



Metric







3 Type

V With anti-twist protection

4 Coding

D With 2 screws and double T-nut





Metric table

Dimensions in: millimeters / inches												
1 s	2 n	7 Bundle Pieces	d1	d2	l1	l2	m1	m2 +0.5	A/F	t +0.5	Tightening torque in Nm	
30 1.18	6 0.24	2	16 0.63	M 6	25.5 1.00	28 1.10	17 0.67	15 0.59	4	12.7 0.50	8	
40 1.57	8 0.31	2	20 0.79	M 8	33.5 1.32	36 1.42	24 0.94	20 0.79	5	16 0.63	25	
60 2.36	6 0.24	2	16 0.63	M 6	25.5 1.00	58 2.28	47 1.85	15 0.59	4	12.7 0.50	8	
80 3.15	8 0.31	2	20 0.79	M 8	33.5 1.32	76 2.99	64 2.52	20 0.79	5	16 0.63	25	

Specification	5	6
Housing		
Zinc die-cast, zinc plated		ZZ
Screws / T-nut		
Steel, zinc plated, blue passivated finish		SZ
RoHS		
Technical Information		Page
Assembly Instructions		QVX

Universal connectors GN 22i fasten aluminum profiles at right angles and secure them against twisting. Only one profile has to be machined. The connection can be freely positioned and slid along the slot. If panels are used in the slot, they must be suitably pocketed. Universal connectors are supplied in bundles. The table shows the quantity included in each bundle.

see also...	Page
GN 22i Universal Connectors (with Single T-Nut)	QVX
GN 10i Aluminum Profiles (Profile Type Light)	QVX
GN 10i Aluminum Profiles (Profile Type Heavy)	QVX

How to order	1 Profile height s
	2 Slot width n
	3 Type
	4 Coding
	5 Material / Finish (Housing)
	6 Material / Finish (Screws and T-nut)
	7 Bundle

1 2 3 4 5 6 7

GN 22i-606-V-D-ZZSZ-2