



- 2** Identification no.
- 3** With stainless steel set screw DIN 913

**Metric table**



Dimensions in: millimeters - inches

d <sub>1</sub> Bore	d <sub>2</sub>	k Clamping length	Length l	t	x <sub>1</sub>	x <sub>2</sub>	y <sub>1</sub>	y <sub>2</sub>	z Screw location for screw size
B 10	5.5 0.22	32 1.26	25 0.98	6 0.24	40 1.57	28 1.10	40 1.57	28 1.10	M6-6
B 12	5.5 0.22	32 1.26	25 0.98	6 0.24	40 1.57	28 1.10	40 1.57	28 1.10	M6-6
B 14	5.5 0.22	32 1.26	25 0.98	6 0.24	40 1.57	28 1.10	40 1.57	28 1.10	M6-6
B 15	5.5 0.22	32 1.26	25 0.98	6 0.24	40 1.57	28 1.10	40 1.57	28 1.10	M6-6
B 16	5.5 0.22	32 1.26	25 0.98	6 0.24	40 1.57	28 1.10	40 1.57	28 1.10	M6-6
B 18	5.5 0.22	32 1.26	25 0.98	6 0.24	40 1.57	28 1.10	40 1.57	28 1.10	M6-6

**Specification**



- Body  
Aluminum
  - Powder coated
  - Black, RAL 9005, textured finish **● SW**
  - Plain, matte shot-blasted finish **○ BL**
- Set screw DIN 913  
Stainless steel AISI 304
- *Stainless Steel Characteristics* → page QVX
- **RoHS compliant**

**Information**

The clamping bore of base plate connector clamps GN 162.8 is not machined, and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw location **z** a set screw reduces the bore cross-section for clamping.

see also...

- *Base Plate Mounting Clamps GN 473* → page QVX
- *Construction Tubes GN 990* → page QVX
- *Base Plate Linear Actuator Connectors GN 162.1* → page QVX

How to order

**GN 162.8-B14-3-SW**

- 1** Bore d<sub>1</sub>
- 2** Identification no.
- 3** Finish