



- 4 Identification no.**
2 With 2 stainless steel socket cap screws DIN 912

Dimensions in: millimeters - inches

| 1 d ₁ Bore | 2 d ₂ Bore | 3 k ₁ Clamping length | k ₂ Clamping length | l ₁ | l ₂ | l ₃ | m | z Screw locations for screw size | Accessory Recommended levers GN 911.9 for z l ₄ | |
|------------------------------------|------------------------------------|---|-----------------------------------|----------------|----------------|----------------|--------------|--|--|------------|
| B 18 | B 18 | 29 1.14 | 30.5 1.20 | 65 2.56 | 34 1.34 | 29 1.14 | 43.5 1.71 | M6-18 | 44 1.73 | 63 2.48 |
| B 30 | B 30 | 44 1.73 | 45.5 1.79 | 96 3.78 | 53 2.09 | 44 1.73 | 64.5 2.54 | M8-25 | 63 2.48 | 78 3.07 |

Specification

- Body
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 212 °F (100 °C)
- Black, RAL 9005, matte finish **S**
- Gray, RAL 7040, matte finish **G**
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 985
- Stainless steel AISI 304
- Self-locking with polyamide ring
- Load Rating Information → page QVX
- Plastic Characteristics → page QVX
- Stainless Steel Characteristics → page QVX
- RoHS compliant

Accessory

- Adapter bushings EN 290 → page QVX
- Adjustable levers GN 911.9 → page QVX

Information

The clamping bores axes of the T-angle connector clamps EN 192.9 lie in the same plane, arranged in a T-shape. They hold typical construction tubes with full surface contact over the entire cross-section of the bore.

At the screw locations z, the socket cap screws reduce the bore cross-section for clamping. Adapter bushings EN 290 can be used to reduce the bore cross-sections to a smaller diameter.

For clamping without tools, the socket cap screws can be replaced by the adjustable levers GN 911.9 listed in the table as accessories.

see also...

- Construction Tubes GN 990 → page QVX

| How to order | 1 Bore d ₁ |
|--------------------------------|----------------------------------|
| | 2 Bore d ₂ |
| | 3 Clamping length k ₁ |
| 1 2 3 4 5 | 4 Identification no. |
| EN 192.9-B30-B30-44-2-S | 5 Color |