



Metric table

Dimensions in: millimeters - inches

| ¹ d ₁ | ² d ₂ Thread | d ₃ | l ₁ | l ₂ min. |
|-----------------------------|---------------------------------------|----------------|----------------|------------------------|
| 14 0.55 | M 5 | 7 0.28 | 34 1.34 | 25 0.98 |
| 23 0.91 | M 6 | 14 0.55 | 60 2.36 | 17 0.67 |
| 23 0.91 | M 8 | 14 0.55 | 60 2.36 | 22 0.87 |
| 26 1.02 | M 8 | 16 0.63 | 70 2.76 | 25 0.98 |
| 26 1.02 | M 10 | 16 0.63 | 70 2.76 | 25 0.98 |
| 30 1.18 | M 10 | 16 0.63 | 65 2.56 | 26 1.02 |
| 30 1.18 | M 12 | 16 0.63 | 65 2.56 | 26 1.02 |
| 35 1.38 | M 12 | 22 0.87 | 85 3.35 | 25 0.98 |
| 35 1.38 | M 16 | 22 0.87 | 85 3.35 | 25 0.98 |

Specification

- Plastic
Duroplast (Phenolic PF)
 - Temperature resistant up to 230 °F (110 °C)
 - Black, shiny finish
 - Molded-in thread
- Plastic Characteristics → page 2135
- RoHS compliant

Information

When using GN 201 elliptical shaped knobs, it must be ensured that the threaded stud is not too short. Otherwise, there is a risk that the Duroplast plastic body could break under certain loads.

These knobs are often used on GN 310 gear lever handles instead of DIN 319 ball knobs.

| | | |
|--|---|--------------------------------|
| How to order ¹ ² GN201-30-M10 | 1 | Handle diameter d ₁ |
| | 2 | Thread d ₂ |