



Metric table

Dimensions in: millimeters - inches

¹ d ₁ f7	² d ₂ H7 Bore with keyway				d ₃	d ₄	l ₁	l ₂	l ₃	³ s	⁴ b	Scale ring set consists of: 2 collar bushing and 1 scale ring body 3 flat springs	
24 .94	K 12	-	-	-	26.7 1.05	18 .71	13.5 .53	5.5 .22	21 .83	.3 .01	10 .39	GN 264-30	GN 374-0.3-10
32 1.26	K 12	K 14	K 16	-	35.7 1.41	25 .98	13.5 .53	5.5 .22	29 1.14	.4 .02	10 .39	GN 264-40	GN 374-0.4-10
50 1.97	K 12	K 16	K 20	K 28	54.7 2.15	38 1.50	14.5 .57	5.5 .22	45 1.77	.6 .02	10 .39	GN 264-60	GN 374-0.6-10
68 2.68	K 12	K 14	K 16	K 22	74.7 2.94	50 1.97	14.5 .57	5.5 .22	60 2.36	.8 .03	10 .39	GN 264-80	GN 374-0.8-10

Specification

- Steel
Plain finish
- Keyways *WN / DIN 6885* → page QVX
- *ISO Fundamental Tolerances* → page QVX
- [RoHS compliant](#)

Information

Two GN 268 collar bushings along with three GN 374 flat springs are required to complete one GN 264 scale ring set.

see also...

- *Scale Rings GN 264 (with and without Scale)* → page QVX

How to order (Collar bushing) GN 268-32-K16	¹ ²	1 Outside diameter d ₁
		2 Bore d ₂
How to order (Flat spring) GN 374-0.3-10	³ ⁴	3 Thickness s
		4 Width b

