



**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> $d_1$	<sup>2</sup> $d_2$ Thread	$d_3$	$l_1$	$l_2$
12 0.47	M 4	9 0.35	40 1.57	8 0.31
15 0.59	M 5	11 0.43	50 1.97	7 0.28
18 0.71	M 6	13 0.51	64 2.52	8 0.31
21 0.83	M 6	15 0.59	72 2.83	10 0.39
21 0.83	M 8	15 0.59	72 2.83	10 0.39
25 0.98	M 8	17 0.67	90 3.54	10 0.39
26 1.02	M 10	20 0.79	100 3.94	12 0.47
33 1.30	M 12	25 0.98	124 4.88	14 0.55

**Specification**

- Plastic  
Duroplast (Phenolic PF)  
- Temperature resistant up to 230 °F (110 °C)  
- Black, shiny finish
- Threaded stud  
Steel, zinc plated, blue passivated finish
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

**Information**

GN 203 fixed tapered handles are used in applications where a positive non-revolving grip is required. They are not suitable for applications where the handle is exposed to heavy loads. For applications with increased loads, see EN 539 cylindrical handles → [www.jwwinco.com](http://www.jwwinco.com).

How to order <sup>1</sup> <sup>2</sup> <b>GN 203-21-M6</b>	<b>1</b> Handle diameter $d_1$
	<b>2</b> Thread $d_2$

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4