



- 3 Identification no.**
- 2** With stainless steel socket cap screw DIN 912

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> d <sub>1</sub> Bore for clamping Ø	<b>2</b> d <sub>2</sub> Bore for sensor	b Swivel width	d <sub>3</sub>	k	l <sub>1</sub>	l <sub>2</sub>	m	t	z Screw location for screw size	<b>Accessory</b> Recommended lever GN 911 for z l <sub>3</sub>		
B 12	B 12	B 18	25 0.98	27 1.06	31.5 1.24	64 2.52	34.5 1.36	29.5 1.16	11 0.43	M6-20	63 2.48	-
B 14	B 12	B 18	25 0.98	27 1.06	31.5 1.24	64 2.52	34.5 1.36	29.5 1.16	11 0.43	M6-20	45 1.77	63 2.48
B 15	B 12	B 18	25 0.98	27 1.06	31.5 1.24	64 2.52	34.5 1.36	29.5 1.16	11 0.43	M6-20	45 1.77	63 2.48
B 16	B 12	B 18	25 0.98	27 1.06	31.5 1.24	64 2.52	34.5 1.36	29.5 1.16	11 0.43	M6-20	45 1.77	63 2.48
B 18	B 12	B 18	25 0.98	27 1.06	31.5 1.24	64 2.52	34.5 1.36	29.5 1.16	11 0.43	M6-20	45 1.77	63 2.48

**Specification**

- Body  
Aluminum  
Powder coated  
Black, RAL 9005, textured finish **SW**
- Socket cap screws DIN 912  
Stainless steel AISI 304
- Hex nuts DIN 985  
Stainless steel AISI 304  
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → page QVX
- **RoHS compliant**

**Information**

The clamping bore of sensor holders GN 275.4 is mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw location **z**, the socket cap screw reduces the bore cross-section for clamping.

For clamping without tools, the socket cap screw can be replaced by an adjustable lever GN 911 listed in the table as accessory.

see also...

- *Construction Tubes GN 990* → page QVX
- *Round Rods / Tubes GN 480.1* → page QVX
- *Attachment Mounting Clamps GN 478* → page QVX

**Accessory**

- Adjustable levers GN 911 → page QVX

<p>How to order</p> <p><b>GN 275.4-B16-B18-2-SW</b></p>	<b>1</b> Bore d <sub>1</sub>
	<b>2</b> Bore d <sub>2</sub>
	<b>3</b> Identification no.
	<b>4</b> Finish