



Metric



**SS** Stainless Steel

Metric table

Dimensions in: millimeters / inches

| <sup>1</sup> d <sub>1</sub> | <sup>2</sup> d <sub>2</sub> | a          | b          | h <sub>1</sub> | h <sub>2</sub> ≈ | Length l ≈  |
|-----------------------------|-----------------------------|------------|------------|----------------|------------------|-------------|
| 16<br>0.63                  | M 8                         | 7<br>0.28  | 12<br>0.47 | 12<br>0.47     | 35<br>1.38       | 56<br>2.20  |
| 20<br>0.79                  | M 10                        | 9<br>0.35  | 14<br>0.55 | 14<br>0.55     | 44<br>1.73       | 70<br>2.76  |
| 25<br>0.98                  | M 12                        | 11<br>0.43 | 18<br>0.71 | 18<br>0.71     | 52<br>2.05       | 87<br>3.43  |
| 32<br>1.26                  | M 16                        | 15<br>0.59 | 22<br>0.87 | 22<br>0.87     | 66<br>2.60       | 109<br>4.29 |
| 40<br>1.57                  | M 20                        | 18<br>0.71 | 28<br>1.10 | 28<br>1.10     | 84<br>3.31       | 140<br>5.51 |

Specification <sup>3</sup>

**Cast iron** —

- Fettled
- Contact faces machined

**Stainless steel precision casting** AISI CF-8 **NI**

- Fettled
- Contact face machined

RoHS

**On request**

- Clamp nuts GN 206, powder coated
- Special inch and metric bores or threads

Clamp nuts GN 206 are simple components. They are a good choice for certain corrosion free environment applications.

see also...

|                                      | Page |
|--------------------------------------|------|
| GN 99.5 Clamp Nuts (Steel)           | QVX  |
| GN 99.6 Clamp Nuts (Stainless Steel) | QVX  |

**Technical Information**

|                                 |     |
|---------------------------------|-----|
| Stainless Steel Characteristics | QVX |
|---------------------------------|-----|

How to order (Steel)

<sup>1</sup> <sup>2</sup>  
**GN 206-32-M16**

- |   |                         |
|---|-------------------------|
| 1 | Diameter d <sub>1</sub> |
| 2 | Thread d <sub>2</sub>   |

How to order (Stainless steel)

<sup>1</sup> <sup>2</sup> <sup>3</sup>  
**GN 206-25-M12-NI**

- |   |                         |
|---|-------------------------|
| 1 | Diameter d <sub>1</sub> |
| 2 | Thread d <sub>2</sub>   |
| 3 | Material                |

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

