



SS Stainless Steel

3 Type

E Angled lever

Inch table

Dimensions in: inches - millimeters

1	2											
d ₁	d ₂		d ₃	d ₄	d ₅	h ₁	h ₃	h ₄ ≈	h ₅ Stroke	l ₂ ≈	l ₃ ≈	t min.
0.83 21	1/4 x 20	5/16 x 18	0.53 13.5	0.31 8	0.79 20	1.32 33.5	0.04 1	2.32 59	0.16 4	2.95 75	2.76 70	0.43 11
0.94 24	5/16 x 18	3/8 x 16	0.63 16	0.39 10	0.98 25	1.57 40	0.10 2.5	2.95 75	0.18 4.5	3.98 101	3.78 96	0.55 14
1.10 28	3/8 x 16	1/2 x 13	0.75 19	0.47 12	1.18 30	1.91 48.5	0.18 4.5	3.50 89	0.18 4.5	4.57 116	4.33 110	0.67 17

Metric table

Dimensions in: millimeters - inches

1	2											
d ₁	d ₂		d ₃	d ₄	d ₅	h ₁	h ₃	h ₄ ≈	h ₅ Stroke	l ₂ ≈	l ₃ ≈	t min.
21 0.83	M 6	M 8	13.5 0.53	8 0.31	20 0.79	33.5 1.32	1 0.04	59 2.32	4 0.16	75 2.95	70 2.76	11 0.43
24 0.94	M 8	M 10	16 0.63	10 0.39	25 0.98	40 1.57	2.5 0.10	75 2.95	4.5 0.18	101 3.98	96 3.78	14 0.55
28 1.10	M 10	M 12	19 0.75	12 0.47	30 1.18	48.5 1.91	4.5 0.18	89 3.50	4.5 0.18	116 4.57	110 4.33	17 0.67

Specification

- Body / lever / insert
Stainless steel AISI 303
Matte shot-blasted finish
- Ball knob DIN 319 → page 55
Plastic
Duroplast (Phenolic PF)
Black, shiny finish
- Safety circlip
Plastic (Polyacetal POM)
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

On request

- Straight lever
- Special threads and stud lengths

Information

GN 212.5 heavy duty adjustable levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The threaded insert is connected with the hub via serrations that can be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

- Heavy Duty Adjustable Levers GN 212.3 (Steel, Blackened Finish) → page 517

How to order (Inch) GN 212.5-21-1/4X20-E	1 Diameter d ₁
	2 Thread d ₂
	3 Type

How to order (Metric) GN 212.5-24-M10-E	1 Diameter d ₁
	2 Thread d ₂
	3 Type