



- 2 Type**  
**OZ** Without centering step (smooth)  
**AV** With external serration  
**IV** With internal serration
- 3 Identification no.**  
**2** With stainless steel socket cap screw DIN 912

Dimensions in: millimeters - inches

d <sub>1</sub> Bore	b Swivel width	d <sub>2</sub>	k	l <sub>1</sub>	l <sub>2</sub>	m	s	t	z Screw location for screw size	Accessory Recommended lever GN 911.9 for z	
										l <sub>3</sub>	
B 30	40 1.57	8.5 0.33	44.5 1.75	95 3.74	44 1.73	42 1.65	13.5 0.53	20 0.79	M8-25	63 2.48	78 3.07

**Specification**

- Body  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 212 °F (100 °C)  
- Black, RAL 9005, matte finish **● SW**  
- Gray, RAL 7040, matte finish **● GR**
- Socket cap screw DIN 912  
Stainless steel AISI 304
- Hex nut DIN 985  
- Stainless steel AISI 304  
- Self-locking with polyamide ring
- [Load Rating Information](#) → page QVX
- [Plastic Characteristics](#) → page QVX
- [Stainless Steel Characteristics](#) → page QVX
- [RoHS compliant](#)

**Accessory**

- Adapter bushings EN 290 → page QVX
- Adjustable levers GN 911.9 → page QVX

**Information**

The fixing lug of the swivel clamp connectors EN 278.9 is available with a smooth surface or with external or internal serration. The clamping bore holds typical construction tubes with full surface contact over the entire cross-section.

At the screw location **z**, the socket cap screw reduces the bore cross-section for clamping. Adapter bushings EN 290 can be used to reduce the bore cross-sections to smaller diameters.

For clamping without tools, the socket cap screw can be replaced by one of the adjustable levers GN 911.9 listed in the table as accessories.

Swivel clamp connectors EN 278.9 can be assembled with swivel clamp connector bases EN 272.9 and swivel clamp connectors EN 276.9 to create swivel clamp connector joints.

see also...

- [Construction Tubes GN 990](#) → page QVX
- [Swivel Clamp T-Angle Connector Joints](#) → page QVX

How to order	1 Bore d <sub>1</sub>
<b>EN 278.9-B30-OZ-2-SW</b>	<b>2 Type</b>
	<b>3 Identification no.</b>
	<b>4 Color</b>