



SS Stainless Steel

3 Type

E Angled lever, with tapped bore

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Thread	d ₄	d ₅	h ₁	h ₂ ≈	l ₁ ≈	l ₂ ≈	t ₁ min.
22 0.87	M 8	8 0.31	20 0.79	37 1.46	67 2.64	89.5 3.52	85 3.35	18 0.71
25 0.98	M 10	10 0.39	25 0.98	42 1.65	76 2.99	100.5 3.96	95 3.74	18 0.71
28 1.10	M 12	12 0.47	30 1.18	47 1.85	87 3.43	114 4.49	108 4.25	20 0.79
32 1.26	M 16	12 0.47	32 1.26	52 2.05	98 3.86	133 5.24	126 4.96	25 0.98

Specification

- Hub / lever
Stainless steel AISI 303
Matte shot-blasted finish
- Ball knob DIN 319 → page 55
Plastic
Duroplast (Phenolic PF)
Black, shiny finish
- Cross Holes GN 110 → page 2042
- Stainless Steel Characteristics → page 2143
- RoHS compliant

4

NI

Information

- GN 212 tension levers are used as clamping devices as well as operating levers.
- see also...
- Heavy Duty Adjustable Levers GN 212.3 (Steel, Blackened Finish) → page 517
 - Heavy Duty Adjustable Levers GN 212.5 (Stainless Steel) → page 520

On request

- Special bores, threads, and threaded studs

How to order	1 Diameter d ₁
	2 Thread d ₂
	3 Type
	4 Material

GN 212-25-M10-E-NI

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4