



Metric table

Dimensions in: millimeters - inches

d ₁	d ₂ Thread	d ₃	h	Length l ±0.25	t min.
18 0.71	M 6	12 0.47	42 1.65	100 3.94	12 0.47
20 0.79	M 8	14 0.55	47 1.85	112 4.41	15 0.59
22 0.87	M 10	16 0.63	53 2.09	125 4.92	18 0.71
25 0.98	M 12	18 0.71	59 2.32	140 5.51	20 0.79

Specification

- Cast iron (GS45)
 - Powder coated
 - Black, RAL 9005, textured finish **● SW**
 - Plain, unfinished casting, deburred **○ BL**
- Contact surface machined
- Load Rating Information → page 2068
- RoHS compliant

On request

- Various metric size fasteners and kit packaging

Information

GN 225 cabinet “U” handles are of simple and solid design. They are best chosen when handles need to be plated or painted.

The tapped holes and contact faces are square and parallel.

see also...

- Round Cabinet “U” Handles GN 425 (Steel) → page 140

How to order

GN 225-20-SW

1	Handle diameter d ₁
2	Finish