


Metric



Assembly example



Metric table

<sup>1</sup> d <sub>1</sub> Linear actuator Ø	b	h	Length l
18 0.71	24 0.94	33 1.30	10 0.39
30 1.18	35 1.38	42 1.65	10 0.39
40 1.57	47 1.85	56.5 2.22	10 0.39
50 1.97	58 2.28	61 2.40	10 0.39
60 2.36	64 2.52	-	7 0.28

Dimensions in: millimeters / inches

Specification <sup>2</sup>

Body

Aluminum  
Anodized finish, black

ELS

Set screw DIN 913

Stainless steel AISI 304

RoHS

Torque supports GN 295.2 are required for attaching a position indicator or a clamping plate to configurable linear actuators.

The torque supports are made of black anodized aluminum and are non-positively clamped to the linear actuator. With the open radial groove on one side, they prevent the position indicator or clamping plate from twisting.

see also...

	Page
GN 2910 Linear Actuators	XYZ
GN 2920 Linear Actuators	XYZ
GN 2930 Linear Actuators	XYZ
EN 9034 Digital Position Indicators (Electronic Counter)	QVX
EN 9534 Digital Position Indicators (Mechanical Counter)	QVX
GN 9734 Clamping Plates	QVX
GN 9234 Handwheels	QVX

Technical Information

Stainless Steel Characteristics QVX

How to order

**GN 295.2-30-ELS**

- <sup>1</sup> Diameter d<sub>1</sub>
- <sup>2</sup> Finish

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10