


Assembly instruction



Metric



Specification

Steel	**ST**
Zinc plated	

RoHS

On request

- Additional clamping ranges
- Other materials

Spring clamps GN 3017.5 secure hose assemblies to hose barbs and hose nipples in low-pressure applications.
The spring force of the bent wire presses onto the elastic hose material to provide a tight connection. The spring clamp is installed by pressing the two arms together with a pliers to open the clamp.

see also...	Page
DIN 3016 Loop Clamps (Steel, with Elastomer Insert)	QVX
DIN 3017 Hose Clamps (Steel / Stainless Steel)	QVX
DIN 3017 T-Bolt Hose Clamps (Steel / Stainless Steel)	QVX

Metric table

Dimensions in: millimeters / inches

d_1 Nominal dimension	d_1 Clamping range Ø	d_2	h max.	VE
6.1 0.24	5.8...6.4 0.23...0.25	0.9 0.04	5 0.20	25
6.8 0.27	6.6...7 0.26...0.28	0.9 0.04	5 0.20	25
7.3 0.29	7...7.5 0.28...0.30	0.9 0.04	5 0.20	25
7.6 0.30	7.3...7.8 0.29...0.31	0.9 0.04	5 0.20	25
8.1 0.32	7.8...8.3 0.31...0.33	0.9 0.04	5 0.20	25
8.6 0.34	8.3...8.8 0.33...0.35	1 0.04	5.5 0.22	25
9.1 0.36	8.8...9.3 0.35...0.37	1 0.04	5.5 0.22	25
9.6 0.38	9.3...9.9 0.37...0.39	1 0.04	5.5 0.22	25
10.1 0.40	9.8...10.4 0.39...0.41	1 0.04	5.5 0.22	25
10.7 0.42	10.4...11 0.41...0.43	1.2 0.05	6.3 0.25	25
11.3 0.44	11...11.6 0.43...0.46	1.2 0.05	6.3 0.25	25
11.9 0.47	11.6...12.3 0.46...0.48	1.2 0.05	6.3 0.25	25
12.8 0.50	12.1...13.1 0.48...0.52	1.2 0.05	6.3 0.25	25
13.3 0.52	12.9...13.6 0.51...0.54	1.5 0.06	7.3 0.29	25
13.7 0.54	13.3...14.1 0.52...0.56	1.5 0.06	7.3 0.29	25
14 0.55	13.6...14.4 0.54...0.57	1.5 0.06	7.3 0.29	25
14.8 0.58	14.4...15.1 0.57...0.59	1.5 0.06	7.3 0.29	25
15.6 0.61	14.8...15.9 0.58...0.63	1.5 0.06	7.3 0.29	25
15.8 0.62	15.5...16.2 0.61...0.64	1.8 0.07	8.4 0.33	25
16.4 0.65	15.9...16.8 0.63...0.66	1.8 0.07	8.4 0.33	25
17.3 0.68	16.8...17.7 0.66...0.70	1.8 0.07	8.4 0.33	25
18.2 0.72	17.7...18.7 0.70...0.74	1.9 0.07	9.1 0.36	25
19.2 0.76	18.7...19.6 0.74...0.77	2 0.08	9.1 0.36	10
20.2 0.80	19.6...20.6 0.77...0.81	2 0.08	9.1 0.36	10
21.2 0.83	20.6...21.6 0.81...0.85	2 0.08	9.1 0.36	10
22.1 0.87	21.5...22.6 0.85...0.89	2 0.08	9.1 0.36	10
22.6 0.89	22...23.1 0.87...0.91	2.2 0.09	10.7 0.42	10
23.1 0.91	22.5...24 0.89...0.94	2.2 0.09	10.7 0.42	10
24.2 0.95	23.5...24.7 0.93...0.97	2.2 0.09	10.7 0.42	10
25.2 0.99	24.4...26 0.96...1.02	2.2 0.09	10.7 0.42	10
25.8 1.02	25.1...26.4 0.99...1.04	2.2 0.09	10.7 0.42	10
26.8 1.06	25.8...27.4 1.02...1.08	2.5 0.10	11.4 0.45	10
27.5 1.08	26.7...28.1 1.05...1.11	2.5 0.10	11.4 0.45	10
28.7 1.13	27.9...29.4 1.10...1.16	2.5 0.10	11.4 0.45	10
30 1.18	29.3...30.9 1.15...1.22	2.5 0.10	11.4 0.45	10
31.3 1.23	30.4...32 1.20...1.26	2.5 0.10	11.4 0.45	10
32.7 1.29	32...34.1 1.26...1.34	2.8 0.11	12.8 0.50	10
34.1 1.34	33.2...34.8 1.31...1.37	2.8 0.11	12.8 0.50	10
35 1.38	33.9...35.7 1.33...1.41	2.8 0.11	12.8 0.50	10
35.6 1.40	34.6...36.4 1.36...1.43	3 0.12	14 0.55	10
37.2 1.46	36.2...38 1.43...1.50	3 0.12	14 0.55	10
38.8 1.53	37.7...39.7 1.48...1.56	3 0.12	14 0.55	5
40 1.57	38...41 1.50...1.61	3 0.12	14 0.55	5
40.5 1.59	39.4...41.4 1.55...1.63	3 0.12	14 0.55	5
42.9 1.69	41...44 1.61...1.73	3.2 0.13	14.8 0.58	5
44.4 1.75	42.5...45.5 1.67...1.79	3.2 0.13	14.8 0.58	5
46 1.81	44...47 1.73...1.85	3.2 0.13	14.8 0.58	5
47 1.85	46...49 1.81...1.93	3.2 0.13	14.8 0.58	5
49.8 1.96	48.4...50.9 1.91...2.00	3.2 0.13	15.9 0.63	5
52 2.05	50.6...53.2 1.99...2.09	3.2 0.13	15.9 0.63	5

How to order

GN 3017.5-12,8-ST

1	**Diameter d_1**
2	**Material**

⚠ **WARNING**: Cancer and Reproductive Harm — www.P65Warnings.ca.gov