



Metric table

2

3

l ₁		l ₂		b	d	m	s	Dimensions in: millimeters / inches	
								Suitable for hinges with hole spacing m	
								GN 235	GN 7231 GN 7233 GN 7237
40	15	25	15	M 5	25	3	x	x	
1.57	0.59	0.98	0.59		0.98	0.12			
50	20	30	20	M 6	30	3	x	x	
1.97	0.79	1.18	0.79		1.18	0.12			
60	20	30	25	M 8	36	4	x	x	
2.36	0.79	1.18	0.98		1.42	0.16			

Specification

14

Plate

Stainless steel AISI 304

Matte, tumbled finish

NI

MT

Threaded studs

Stainless steel AISI 416 / AISI 304CU

Pressed-in

RoHS

On request

• Other threaded stud lengths

• Other plate sizes

• Other plate geometries

Mounting plates with threaded studs GN 2376 are designed as accessories for several hinge variations. They eliminate the need for additional threads, screws, nuts, and washers for mounting. There is no need for the time-consuming pre-assembly of the above components or for counterholding during tightening or loosening.

The mounting plates are mounted from the outside via through-holes in the housing wall or alternatively by welding to the inside of the wall. This results in effective protection against vandalism, and the housing exteriors remain free of attachments that do not match the design or that should be avoided entirely in the interests of easy cleaning.

see also...	Page
GN 2372 Spacer Plates (with Tapped Holes)	QVX
GN 2370 Spacer Plates	QVX
GN 2374 Limit Stops	QVX

Technical Information	QVX
Stainless Steel Characteristics	

How to order	1	Material
	2	Length l ₁
	3	Thread length l ₂
	4	Finish
GN 2376-NI-40-15-MT		