



SS Stainless Steel

**Metric table**

Dimensions in: millimeters - inches

l <sub>1</sub>	l <sub>2</sub>		b	d	m	s	Suitable for hinges with hole spacing m		
							GN 235	GN 7231 GN 7233 GN 7237	
40 1.57	15 0.59	25 0.98	15 0.59	M 5	25 0.98	3 0.12	x	x	
50 1.97	20 0.79	30 1.18	20 0.79	M 6	30 1.18	3 0.12	x	x	
60 2.36	20 0.79	30 1.18	25 0.98	M 8	36 1.42	4 0.16	x	x	

**Specification**

- Body  
Stainless steel AISI 304  
Matte, tumbled finish
- Threaded studs  
Stainless steel AISI 304  
Pressed-in
- *Stainless Steel Characteristics* → page 2143
- [RoHS compliant](#)

1 4

NI MT

**On request**

- Other threaded stud lengths
- Other plate sizes
- Other plate geometries

**Information**

GN 2376 mounting plates with threaded studs are designed as accessories for several hinge variations. They eliminate the need for additional threads, screws, nuts, and washers for mounting. There is no need for the time-consuming pre-assembly of the above components or for counterholding during tightening or loosening.

The mounting plates are mounted from the outside via through-holes in the housing wall or alternatively by welding to the inside of the wall. This results in effective protection against vandalism, and the housing exteriors remain free of attachments that do not match the design or that should be avoided entirely in the interests of easy cleaning.

see also...

- *Spacer Plates with Tapped Holes GN 2372* → page 1381
- *Spacer Plates GN 2370* → page 1380
- *Limit Stops GN 2374* → page 1336

How to order	
1	Material
2	Length l <sub>1</sub>
3	Thread length l <sub>2</sub>
4	Finish

1 2 3 4  
**GN 2376-NI-40-15-MT**