



Inch table

1 2

Dimensions in: inches - millimeters

l_1	d_1 Thread			d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.
1.77 45	10 x 32	10 x 24	1/4 x 20	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5	0.35 9
2.48 63	1/4 x 20	5/16 x 18	-	0.53 13.5	0.69 17.5	1.22 31	0.26 6.5	1.12 28.5	0.16 4	0.43 11
3.07 78	5/16 x 18	3/8 x 16	-	0.63 16	0.83 21	1.42 36	0.31 8	1.34 34	0.16 4	0.55 14

Metric table

1 2

Dimensions in: millimeters - inches

l_1	d_1 Thread			d_3	d_4	h_1	h_2	h_3	h_4 Stroke	t min.
22 0.87	M 3	M 4	M 5	8 0.31	10.5 0.41	18.5 0.73	2 0.08	16.5 0.65	3 0.12	5 0.20
30 1.18	M 4	M 5	M 6	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14	9 0.35
45 1.77	M 4	M 5	M 6	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14	9 0.35
63 2.48	M 6	M 8	-	13.5 0.53	17.5 0.69	31 1.22	6.5 0.26	28.5 1.12	4 0.16	11 0.43
78 3.07	M 8	M 10	-	16 0.63	21 0.83	36 1.42	8 0.31	34 1.34	4 0.16	14 0.55

Specification

3

- Lever body
Zinc die-cast
- Powder coated
 - Black, RAL 9005, textured finish **SW**
 - Orange, RAL 2004, textured finish **OS**
 - Red, RAL 3000, textured finish **RS**
 - Silver, RAL 9006, textured finish **SR**
- Insert / retaining screw
Steel, zinc plated, blue passivated finish
- RoHS compliant

Information

GN 302.2 adjustable levers have a straight lever parallel to the clamping surface. For some applications this presents an advantage due to limits of space or for visual reasons.

These levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

- Straight Adjustable Levers GN 302 (Steel Insert, Blackened Finish)
- Straight Adjustable Levers GN 302.1 (Stainless Steel Insert)
- Adjustable Levers GN 300.2 (Steel Insert, Zinc Plated)

How to order (Inch)	1 Lever length l_1
GN 302.2-45-1/4X20-SW	2 Thread d_1
	3 Color

How to order (Metric)	1 Lever length l_1
GN 302.2-63-M6-SW	2 Thread d_1
	3 Color