



Metric table

Dimensions in: millimeters - inches

¹ d ₀ = Shaft collar Ø d ₁		² d ₁	³ h ₂	d ₂	d ₃	l ₂	h ₁	h ₃	
30 1.18	32 1.26	30 1.18	M 4	12 0.47	7.2 0.28	13 0.51	12 0.47	32 1.26	30 1.18
36 1.42	-	30 1.18	M 5	13 0.51	8.7 0.34	13 0.51	14 0.55	33.5 1.32	31 1.22
42 1.65	-	30 1.18	M 5	15 0.59	8.7 0.34	13 0.51	14 0.55	35 1.38	33 1.30
48 1.89	-	45 1.77	M 5	16 0.63	8.7 0.34	13 0.51	16 0.63	36.5 1.44	34 1.34
55 2.17	-	45 1.77	M 6	18 0.71	10 0.39	13 0.51	16 0.63	38.5 1.52	36 1.42
60 2.36	-	45 1.77	M 6	19 0.75	10 0.39	13 0.51	16 0.63	39.5 1.56	37 1.46
65 2.56	-	45 1.77	M 6	20 0.79	10 0.39	13 0.51	18 0.71	40.5 1.59	38 1.50

Specification

- Lever body
Zinc die-cast, powder coated
Black, RAL 9005, textured finish **● SW**
- Threaded stud
Stainless steel AISI 303
- Retaining screw
Stainless steel AISI 304
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

For shaft collars of the series GN 706... and GN 707..., the GN 311 adjustable lever replaces the DIN 912 socket cap screw. The lever allows the shaft collars to be adjusted easily and quickly without tools.

The table of dimensions of these shaft collars shows the suitable adjustable lever for the respective shaft collar size d₁.

Semi-split shaft collars GN 706.2 including adjustable lever are available under GN 706.4.

see also...

- Semi-Split Shaft Collars GN 706.2 → page 1206
- Split Shaft Collars GN 707.2 → page 1214

How to order	¹ Lever length l ₁
	² Thread d ₁
	³ Height h ₂
	⁴ Color

GN 311-¹30-²M5-³15-⁴SW