

3 Type

- BJ** Adjustable on both sides
- EJ** Adjustable on one side
- NJ** Not adjustable

Metric table

1	2	Dimensions in: millimeters - inches								
l_1	l_2	d_1	d_2	$h_1 \approx$	$h_2 \approx$	h_3	l_3	m_1	m_2	
42 1.65	42 1.65	5.3 0.21	4 0.16	11 0.43	6.5 0.26	7.5 0.30	17 0.67	25 0.98	25 0.98	
50 1.97	50 1.97	6.3 0.25	5 0.20	13.5 0.53	7 0.28	8.5 0.33	21 0.83	30 1.18	30 1.18	
60 2.36	60 2.36	6.3 0.25	6 0.24	16.5 0.65	8.5 0.33	11 0.43	26 1.02	36 1.42	36 1.42	

Specification

- **Body**
Zinc die-cast, powder coated
Black, RAL 9005, textured finish
Silver, RAL 9006, textured finish
- **Adjustable disk**
Steel, hardened
- **Cover cap**
Plastic
- Black-gray for SW
- Light gray for SR
- **Pin**
Stainless steel AISI 303
- **Load Rating Information** → page 2088
- **Stainless Steel Characteristics** → page 2143
- **RoHS compliant**


Information

- GN 238 hinges allow a technically and visually perfect alignment of the door to its frame. Hinge is available with both sides adjustable (Type BJ), one side adjustable (Type EJ), and fixed hole type (Type NJ).
- The steel adjustable disk has a serrated ring on its bottom side that seats into the radially positioned serrations of the zinc hinge plate when the countersunk screw is tightened. This secures the disk in place (patented).
- The plastic cover hides the adjustable disk and the screw to prevent dirt from entering, and also provides a clean, appealing look.
- see also...**
- **List of Hinge Types** → page 1324
 - **Adjustable Alignment Hinges GN 127 (Zinc Die-Cast)** → page 1404
 - **Hinges EN 236 (Technopolymer Plastic, Adjustable)** → www.jwwinco.com


<p>How to order</p> <p>GN 238-50-50-BJ-SW</p>	1	Width l_1
	2	Length l_2
	3	Type
	4	Color



Swiveling range



Operating principle (Type BJ)



Assembly instruction

