Hinges

Zinc Die-Cast, Adjustable, with Cover Caps



Adjustable version



Non-adjustable version



Metric

iF product design award

3 Type

BJ Adjustable on both sides
EJ Adjustable on one side
NJ Not adjustable

Type **BJ**



Type **EJ**



Type **NJ**



Metric table

Dimensions in: millimeters / inches

1 l_1	2 l_2	d_1	d_2	h_1 ≈	h_2 ≈	h_3	l_3	m_1	m_2
42 1.65	42 1.65	5.3 0.21	4 0.16	11 0.43	6.5 0.26	7.5 0.30	17 0.67	25 0.98	25 0.98
50 1.97	50 1.97	6.3 0.25	5 0.20	13.5 0.53	7 0.28	8.5 0.33	21 0.83	30 1.18	30 1.18
60 2.36	60 2.36	6.3 0.25	6 0.24	16.5 0.65	8.5 0.33	11 0.43	26 1.02	36 1.42	36 1.42

Specification

4

Hinge leafs
Zinc die-cast
Powder coated
- Black, RAL 9005, textured finish ● **SW**
- Silver, RAL 9006, textured finish ○ **SR**

Adjustable disk
Stainless steel AISI 303

Cover caps
Plastic
- Black-gray for SW
- Light gray for SR

Pin
Stainless steel AISI 303

RoHS

Technical Information	Page
Swiveling Range	QVX
List of Cam Latch / Cam Lock Types	QVX
Load Rating Information	QVX
Stainless Steel Characteristics	QVX

Hinges GN 238 allow a technically and visually perfect alignment of the door to its frame.
Hinge is available with both sides adjustable (Type BJ), one side adjustable (Type EJ), and fixed hole type (Type NJ).
The steel adjustable disk has a serrated ring on its bottom side that seats into the radially positioned serrations of the zinc hinge plate when the countersunk screw is tightened. This secures the disk in place (patented).
The plastic cover hides the adjustable disk and the screw to prevent dirt from entering, and also provides a clean, appealing look.

see also...	Page
GN 127 Hinges	QVX
EN 236 Hinges (Technopolymer Plastic, Adjustable)	QVX

How to order

1 2 3 4
GN 238-50-50-BJ-SW

1	**Width l_1**
2	**Length l_2**
3	**Type**
4	**Color**

⚠ **WARNING**: Cancer and Reproductive Harm — www.P65Warnings.ca.gov

Swivelling Range



Operating Principle (Type BJ)



Assembly Instruction



⚠ WARNING: Cancer and Reproductive Harm — www.P65Warnings.ca.gov