




Metric table

2

A/F	b ₁ ≈	b ₂ ≈	d ≈	h	Length l ≈
7 0.28	15 0.59	6 0.24	12 0.47	5 0.20	100 3.94
8 0.31	17 0.67	7 0.28	13 0.51	5 0.20	105 4.13
10 0.39	21 0.83	9 0.35	16 0.63	5 0.20	125 4.92
11 0.43	23 0.91	9.5 0.37	18 0.71	5 0.20	135 5.31
13 0.51	27 1.06	11 0.43	21 0.83	5 0.20	150 5.91
14 0.55	30 1.18	12 0.47	23 0.91	5 0.20	155 6.10
15 0.59	32 1.26	16 0.63	24 0.94	6 0.24	160 6.30
16 0.63	33 1.30	14 0.55	26 1.02	6 0.24	165 6.50
17 0.67	36 1.42	15 0.59	28 1.10	6 0.24	170 6.69
18 0.71	38 1.50	15 0.59	29 1.14	6 0.24	175 6.89
19 0.75	40 1.57	17 0.67	31 1.22	6 0.24	180 7.09
22 0.87	46 1.81	19 0.75	36 1.42	8 0.31	185 7.28
24 0.94	50 1.97	21 0.83	39 1.54	8 0.31	200 7.87
27 1.06	56 2.20	23 0.91	44 1.73	8 0.31	220 8.66
30 1.18	63 2.48	26 1.02	48 1.89	10 0.39	240 9.45

Dimensions in: millimeters / inches

Specification	4	5
Aluminum	AL	
Matte finish		M
• Tumbled for A/F 7 ... A/F 19		
• Chamfered for A/F 22 ... A/F 30		
RoHS		
Technical Information		Page
Product Family Hygienic Design		QVX

Combination wrenches GN 3113 are used to assemble and adjust Hygienic Design standard parts with two or six wrench flats.

In conjunction with the aluminum material used, the rounded geometry of the wrench surfaces transfers the torque to the screw head without causing damage.

The combination wrenches are designed for manual operation with moderate torques.

see also...	Page
GN 1580 Hex Head Screws (Stainless Steel, Hygienic Design)	QVX
GN 1581 Hex Head Screws (Stainless Steel, Low-Profile Head, Hygienic Design)	QVX
GN 1582 Hex Head Screws (Stainless Steel, with Thin Shaft, Hygienic Design)	QVX
GN 1150 Cam Latches	
(Stainless Steel, Operating and Latch Arm Side in Hygienic Design)	QVX
GN 19 Leveling Feet (Stainless Steel, Foot Plate Sheet Metal, Hygienic Design)	QVX
GN 20 Leveling Feet (Stainless Steel, Hygienic Design)	QVX

How to order	1 Coding
	2 A/F
	3 Type
	4 Material
	5 Finish

1

2

3

4

5

GN3113-RM-16-SF-ALM