



Metric



SS Stainless Steel

3 Type

A With countersunk holes

Metric table

1 2

Dimensions in: millimeters / inches

l ₁		l ₂	d ₁		h ₁	h ₂ ≈	l ₃	m ₁	m ₂	m ₃	m ₄	s
Steel	Stainless steel			For countersunk screws								
85 3.35	-	70 2.76	5.5 0.22	M 4	6.5 0.26	12 0.47	75 2.95	65 2.56	45 1.77	45 1.77	10 0.39	1.3 0.05
100 3.94	100 3.94	80 3.15	5.5 0.22	M 4 / M 5	7.5 0.30	14 0.55	95 3.74	75 2.95	52 2.05	44 1.73	22.5 0.89	1.5 0.06
120 4.72	-	95 3.74	5.5 0.22	M 5	7.5 0.30	15 0.59	103.5 4.07	96 3.78	70 2.76	55 2.17	20 0.79	1.5 0.06
135 5.31	-	110 4.33	6.4 0.25	M 6	10 0.39	15 0.59	123 4.84	105 4.13	75 2.95	73 2.87	22 0.87	1.8 0.07

Specification

4

Steel	ST
Zinc plated, blue passivated finish	
Stainless steel AISI 304	NI
Plain finish	
RoHS	

Folding handles GN 3136 are used for pulling out drawers or lifting boxes and containers. When in use, the swivel handle strikes the sheet metal housing at around 90° and then returns to its rest position by gravity.

Due to the simple design, the stamped and bent parts can have larger tolerances. Appropriate compensation measures should therefore be considered in the design.

see also...

	Page
GN 425.8 Folding Handles with Recessed Tray (with Locking or Spring-Loaded Return)	QVX
GN 425.9 Folding Handles (Stainless Steel, with / without Retaining Spring)	QVX
EN 825.1 Folding Handles (Plastic, with Spring-Loaded Return)	QVX

Technical Information

Stainless Steel Characteristics	QVX
---------------------------------	-----

How to order

1 2 3 4
GN 3136-100-80-A-ST

- 1 Length l₁
- 2 Length l₂
- 3 Type
- 4 Material

