



SS Stainless Steel

Specification

- Crank body
Stainless steel precision casting AISI CF-8
Contact face of hub machined
- Revolving handle similar to GN 598.1
→ page 39
Plastic
Black, shiny finish
- Threaded spindle
Stainless steel AISI 304
- Square Bores DIN 79 → page 2044
- Cross Holes GN 110 → page 2042
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- [RoHS compliant](#)

On request

- Other modifications such as special inch and metric bores, keyways, set screw holes, etc
- Stainless steel crank handles with GN 798.5 stepped retractable handle → page 48

Information

GN 269 straight crank handles have been designed to comply with stringent hygiene requirements. The cylindrical handles are made of Duroplast, which provides good resistance to chemicals.

<p>How to order (Inch)</p> <p style="text-align: center;">1 2</p> <p>GN 269-80-B1/2</p>	<p>1 Length l</p> <hr/> <p>2 Bore d₁</p>
<p>How to order (Metric)</p> <p style="text-align: center;">1 2</p> <p>GN 269-125-V14</p>	<p>1 Length l</p> <hr/> <p>2 Square s (Bore d₁)</p>

Inch table

Dimensions in: inches - *millimeters*

Length 1	2 d ₁ +0.002 Bore	d ₂	h ₁	h ₂ ≈	h ₃	h ₄ ≈	Ø Handle
3.15 80	B 1/2	0.87 22	0.87 22	0.61 15.4	0.26 6.6	1.77 45	0.71 18
3.94 100	B 1/2	1.02 26	1.02 26	0.70 17.7	0.33 8.3	2.17 55	0.83 21
4.92 125	B 5/8	1.10 28	1.10 28	0.74 18.8	0.36 9.2	2.80 71	0.91 23
6.30 160	B 3/4	1.26 32	1.26 32	0.89 22.6	0.37 9.4	2.80 71	0.91 23

Metric table

Dimensions in: millimeters - *inches*

Length 1	2 d ₁ H9 Bore	2 s H11 Square	d ₂	h ₁	h ₂ ≈	h ₃	h ₄ ≈	Ø Handle
80 3.15	B 10	V 10	22 0.87	22 0.87	15.4 0.61	6.6 0.26	45 1.77	18 0.71
100 3.94	B 12	V 12	26 1.02	26 1.02	17.7 0.70	8.3 0.33	55 2.17	21 0.83
125 4.92	B 14	V 14	28 1.10	28 1.10	18.8 0.74	9.2 0.36	71 2.80	23 0.91
160 6.30	B 17	V 17	32 1.26	32 1.26	22.6 0.89	9.4 0.37	71 2.80	23 0.91
200 7.87	B 19	V 19	38 1.50	38 1.50	28 1.10	9.4 0.37	71 2.80	23 0.91

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

