



Metric



SS Stainless Steel

3 Type

A With countersunk holes

Metric table

Dimensions in: millimeters / inches

1		2											
l_1		l_2	d_1		h_1	$h_2 \approx$	l_3	m_1	m_2	m_3	m_4	s	
85 3.35	-	70 2.76	5.5 0.22	M 4	6.5 0.26	12 0.47	75 2.95	65 2.56	45 1.77	45 1.77	10 0.39	1.3 0.05	
100 3.94	100 3.94	80 3.15	5.5 0.22	M 4 / M 5	7.5 0.30	14 0.55	95 3.74	75 2.95	52 2.05	44 1.73	22.5 0.89	1.5 0.06	
120 4.72	-	95 3.74	5.5 0.22	M 5	7.5 0.30	15 0.59	103.5 4.07	96 3.78	70 2.76	55 2.17	20 0.79	1.5 0.06	
135 5.31	-	110 4.33	6.4 0.25	M 6	10 0.39	15 0.59	123 4.84	105 4.13	75 2.95	73 2.87	22 0.87	1.8 0.07	

Specification

Steel

- Zinc plated, blue passivated finish
- Powder coated
- Black, RAL 9005, textured finish

ST

● **STSW**

Stainless steel AISI 304

Plain finish

NI

RoHS

Folding handles GN 3136 are used for pulling out drawers or lifting boxes and containers. When in use, the swivel handle strikes the sheet metal housing at around 90° and then returns to its rest position by gravity.

Due to the simple design, the stamped and bent parts can have larger tolerances. Appropriate compensation measures should therefore be considered in the design.

see also...

Page

GN 425.8 Folding Handles with Recessed Tray (with Locking or Spring-Loaded Return)	QVX
GN 425.9 Folding Handles (Stainless Steel, with / without Retaining Spring)	QVX
EN 825.1 Folding Handles (Plastic, with Spring-Loaded Return)	QVX

Technical Information

Load Capacity Information	QVX
Stainless Steel Characteristics	QVX

How to order

GN 3136-100-80-A-ST

- 1 Length l_1
- 2 Length l_2
- 3 Type
- 4 Material