


- 3 Type**
- N Nut without increased torque
- 4 Coding**
- C With fastening set

Use



Specification

- Connector, screws, T-slot nuts
Steel, zinc plated,
blue passivated finish **SZ**
- Cover cap
Plastic
Technopolymer (Polyamide PA)
Black **S**
- Guide pin
Plastic, black
- *Plastic Characteristics* → page QVX
- **RoHS**

Information

Bolt connectors GN 26b fasten aluminum profiles at right angles and secure them against twisting. Only one profile has to be machined.

The connection can be freely positioned and slid along the slot. It is suitable for absorbing high loads, including torsional loads in particular.

The cover caps ensure a visually appealing appearance. If panels are used, they must be suitably pocketed.

see also...

- *Aluminum Profiles GN 10b (Profile Type Light)* → page QVX
- *Aluminum Profiles GN 10b (Profile Type Heavy)* → page QVX

How to order

GN 26b-90 10-N-C-SZ S

1	Length l ₁
2	Slot width n
3	Type
4	Coding
5	Material / Finish
6	Color of the cover cap

Metric table

Dimensions in: millimeters - inches

¹ l_1 Nominal size	² n	d_1	d_2	d_3	$l_2 \approx$	m_1	m_2	Tightening torque in Nm
30 1.18	8 0.31	M 5	7.3 0.29	11 0.43	29 1.14	18 0.71	18 0.71	6
40 1.57	10 0.39	M 8	10 0.39	17 0.67	37 1.46	23 0.91	22.5 0.89	25
45 1.77	10 0.39	M 8	10 0.39	17 0.67	42 1.65	28 1.10	22.5 0.89	25
60 2.36	10 0.39	M 8	10 0.39	17 0.67	57 2.24	43 1.69	22.5 0.89	25
80 3.15	10 0.39	M 8	10 0.39	17 0.67	77 3.03	63 2.48	22.5 0.89	25
90 3.54	10 0.39	M 8	10 0.39	17 0.67	87 3.43	73 2.87	22.5 0.89	25

Assembly Instructions / Profile Machining

