



- 3 Identification no.**
- 2** With stainless steel socket cap screw DIN 912

**Metric table**

Dimensions in: millimeters - inches

<b>1</b> $d_1$ Bore for clamping $\varnothing$	<b>2</b> $d_2$ Bore for sensor	$b$ Swivel width	$d_3$	$k$	$l_1$	$l_2$	$m$	$t$	$z$ Screw location for screw size	<b>Accessory</b> Recommended lever GN 911 for $z$ $l_3$		
B 20	B 18	B 30	40 1.57	50 1.97	42.5 1.67	92 3.62	52 2.05	72 2.83	10 0.39	M8-25	-	-
B 25	B 18	B 30	40 1.57	50 1.97	42.5 1.67	92 3.62	52 2.05	72 2.83	10 0.39	M8-25	63 2.48	78 3.07
B 30	B 18	B 30	40 1.57	50 1.97	42.5 1.67	92 3.62	52 2.05	72 2.83	10 0.39	M8-25	63 2.48	78 3.07

**Specification**

- Body  
Aluminum  
Powder coated  
Black, RAL 9005, textured finish **SW**
- Socket cap screws DIN 912  
Stainless steel AISI 304
- Hex nuts DIN 985  
Stainless steel AISI 304  
Self-locking via polyamide ring
- *Stainless Steel Characteristics* → page QVX
- **RoHS compliant**

**Information**

The clamping bore of sensor holders GN 276.4 is mechanically machined and designed for construction tubes GN 990 or DIN 2391, DIN 2395 and DIN 2462.

At the screw location  $z$ , the socket cap screw reduces the bore cross-section for clamping.

For clamping without tools, the socket cap screw can be replaced by an adjustable lever GN 911 listed in the table as accessory.

**see also...**

- *Construction Tubes GN 990* → page QVX
- *Round Rods / Tubes GN 480.1* → page QVX
- *Attachment Mounting Clamps GN 478* → page QVX

**Accessory**

- Adjustable levers GN 911 → page QVX

<p><b>How to order</b></p> <p><b>GN 276.4-B20-B18-2-SW</b></p>	<b>1</b> Bore $d_1$
	<b>2</b> Bore $d_2$
	<b>3</b> Identification no.
	<b>4</b> Finish