Characteristics of the standard versions GN 332

GN 332 tubular handles have the CE marking, low voltage guideline 2014 / 35 / EU

Emergency stop	2-channel, normally closed contact	
1st button with 2 LED	Changeover contact	
	LED, red and green	
2nd button	Normally open contact	
Contact termination, pin configuration	Plug M12x1, 12-pole	
Switching voltage / switching current	Max. 24 V DC / max. 0.5 A	
Operating voltage (LEDs)	24 V DC ±15% / 10 mA	
Protection class	IP 67 (in screwed condition)	
Button color	For each button a set of caps is included in the colors red, green, blue	

Additional variations as special version

Emergency stop	1-channel	
Number of buttons > 2 **Button optional with**	Normally open contact	
	Normally closed contact	
	Changeover contact	
Button with labeling area