



Metric table

d <sub>1</sub>	h <sub>1</sub>	b	d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	d <sub>5</sub>	d <sub>6</sub>	h <sub>2</sub>	m	A/F	t min.
For rod / tube											
30 <sup>+0.1 -0.25</sup> 1.181 <sup>+0.004 -0.01</sup>	60 2.36	27.5 1.08	M 10	46 1.81	46.6 1.83	42 1.65	8 0.31	84 3.31	13.5 0.53	5	20 0.79
40 <sup>+0.15 -0.3</sup> 1.575 <sup>+0.006 -0.012</sup>	70 2.76	30 1.18	M 12	56 2.20	56.8 2.24	50 1.97	8 0.31	99 3.90	18.5 0.73	5	25 0.98

Specification	1	4	5
<b>Handle leg</b>			
Stainless steel AISI 304	NI		
Matte finish (Ra < 0.8 µm)		MT	
<b>Sealing ring / Wiper</b>			T
TPU			
• Blue			
• Operating temperature -4 °F to +230 °F (-20 °C to +110 °C)			
• Hardness 95 ±5 Shore A			
• FDA compliant			
<b>Clamping wedge</b>			
Brass			
<b>Set screw</b>			
Stainless steel			
RoHS			
<b>Accessory</b>			Page
GN 1580 Hex Head Screws			QVX
GN 1581 Hex Head Screws			QVX

Handle legs GN 3331 comply with the DGUV testing principles and are intended for use in hygienic areas. The sealed mounting surface enables fastening without dead spaces. The high quality finish as well as the non-concave geometry prevent adherence of dirt and facilitate cleaning. The straight handle legs are designed for use with tubular handles GN 3330 to reduce large distances between mounting points or excessive loads on the handle legs. Regardless of the handle application, supports can be used to fix rods and tubes with the corresponding diameter d<sub>1</sub>. The tube or rod is fastened during installation using the integrated clamping wedge.

see also...	Page
GN 3330 Tubular Handles (Stainless Steel, Hygienic Design)	QVX

Technical Information	
Product Family Hygienic Design	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX

How to order	
1	Material
2	Diameter d <sub>1</sub>
3	Height h <sub>1</sub>
4	Finish
5	Sealing ring material

GN3331-NI-40-70-MT-T